






Article-No.	Length	EAN-Code	Head	Handles	Cutting Capacities				
					Ømm	Ømm	Ømm	mm ²	g
03 00	160	015154	polished	black afromentized, chequered	3.1	2.0	10.0	16	180
	180	015161			3.4	2.2	12.0	16	200
	200	015178			3.8	2.5	13.0	16	260
	250	015185			3.8	2.5	15.0	25	440
03 01	140	015192	polished	plastic-coated	2.8	1.8	9.0	10	100
	160	013235			3.1	2.0	10.0	16	180
	180	013242			3.4	2.2	12.0	16	210
	200	013259			3.8	2.5	13.0	16	270
03 02	160	014430	polished	heavy insulated	3.1	2.0	10.0	16	200
	180	014034			3.4	2.2	12.0	16	230
	200	014997			3.8	2.5	13.0	16	320
03 05	140	015246	chrome plated	heavy insulated	2.8	1.8	9.0	10	120
	160	014829			3.1	2.0	10.0	16	200
	180	014836			3.4	2.2	12.0	16	240
	200	015284			3.8	2.5	13.0	16	310
03 06	160	000532	chrome plated	heavy insulated,  VDE-tested  1000 V	3.1	2.0	10.0	16	200
	180	000549			3.4	2.2	12.0	16	230
	200	000556			3.8	2.5	13.0	16	320
03 07	160	015307	chrome plated	plastic-dipped,  VDE-tested  1000 V	3.1	2.0	10.0	16	245
	180	015314			3.4	2.2	12.0	16	290
	200	015321			3.8	2.5	13.0	16	345
	250	015345			3.8	2.5	15.0	25	585

- ▶ cutting edges for hard and soft wire
- ▶ oil-hardened and tempered
- ▶ cutting edges separately induction-hardened
- ▶ cutting edge hardness approx. 60 HRC
- ▶ Material: special tool steel, oil-hardened


03 Combination Pliers

special tool steel


DIN ISO 5746



03 01 200




03 06 180




Article-No.	Length	EAN-Code	Head	Handles	g
08 05	110	015383	chr. plated	heavy insulated	70
08 15	110	015390	chr. plated	as No. 08 05, with suitable leather pouch	80

- ▶ high quality pliers for hobbyists
- ▶ for hard and soft wires
- ▶ cutting edges separately induction-hardened
- ▶ Material: Chrome Vanadium electric steel, oil-hardened

08 Small Combination Pliers



08 05 110



08 15 110