

## mounting styles

**S** - standard mounting kit

**B** - resin center potting with brass inserts

**H** - resin center potting with troughhole

**D** - DIN 35 (rail)



**S**

**B**

**H**



**D** (12-32 VA)

**D** (50-160 VA)

**D** (200-300 VA)

output [VA]	B brass insert under screw	H screw hole	S height increase [mm]	D height increase [mm]
12-32	M4	M4	2,5	8
50-160	M6	M5	2,5	10
200-300	M8	M8	2,5	8
400-800	M8	M8	2,5	-

ordering key

**58 - 0012 - 012 - x**

mounting style

secondary [V]

output [VA]

internal code

## custom-designed mounting



© 2000 TALEMA electronic s.r.o. All rights reserved.

© Adobe, the Adobe logo is a trademark of Adobe Systems Inc.

Design by: Bedřich