

Section Links

A045 | A040 | A095 | A090 | A195 | A190 | A080 | A085 | A087 | **A200** | A070 | A210 | A300 | A315 | A089 | A125 | A105 | A205

Product Details

A200 Low Profile Bolt Down Stainless Steel Base and Stud

Materials Base - Stainless Steel, type 303
Stud - Stainless Steel, type 303



Part No.	Thread Size D1 (mm)	Thread Length L (mm)	Base Diameter D2 (mm)	Bolt Down Centres C1 (mm)	Overall Height H (mm)	Flange Thickness t (mm)	Hole Diameter d (mm)	Maximum Recommended Load (kg)
A200/001	M8	60	50	40	82	4	5.5	300
A200/002	M10	75	50	40	97	5	5.5	500
A200/003	M12	75	50	40	100	4	5.5	750
A200/006	M12	75	60	50	100	5	5.5	1250
A200/007	M12	125	60	50	150	5	5.5	1250
A200/008	M12	150	60	50	175	5	5.5	1250
A200/009	M16	75	80	68	106	6	6.5	1750
A200/010	M16	125	80	68	156	6	6.5	1750
A200/011	M16	150	80	68	181	6	6.5	1750
A200/014	M16	125	100	82	158	6.5	9	2500
A200/015	M16	150	100	82	183	6.5	9	2500
A200/016	M16	200	100	82	233	6.5	9	2500
A200/017	M20	125	100	82	164	6.5	9	2500
A200/018	M20	150	100	82	189	6.5	9	2500
A200/019	M20	200	100	82	239	6.5	9	2500
A200/022	M20	150	120	100	191	7.5	11	3750
A200/023	M20	200	120	100	241	7.5	11	3750
A200/025	M24	125	120	100	181	7.5	11	3750
A200/026	M24	150	120	100	206	7.5	11	3750
A200/027	M24	200	120	100	256	7.5	11	3750

Dimensions are approximate

