

XCMQ2
Component - Thermal Cutoffs

February 4, 1992

NEC CORP

E71747 (N)

9-1 2-CHOME SEIRAN OTSU , SHIGA 520 JAPAN

Types SF70, 70, -91, -96, -99, -109, -119, -129, -139, -152, -169, -188, -214, -226, -240 with suffix E or U and additional optional suffix 1.

Types SM065B, SM095B, -098A, -098B, -110B, -126B, -130B, -145B, followed by 0 or 1.

Types SM065A, -078A, -095A, -110A, -126A, -129A, -130A, -145A, -164A, -182A followed by 0 or 1.

Types SF109Y, -119Y, -129Y, -152Y with or without suffix 1.

Types SM095D, -110D, -126D, -130D, -145D followed by 0 or 1.

Type SM095G, -110G, -126G, -130G, -145G followed by 0 or 1.

Marking: Company name or trade-mark "SEFUSE" and type designation.

See General Information Preceding These Recognitions.

For use only in equipment where the acceptability of the combination is determined by Underwriters Laboratories Inc.

Reports: April 23, 1981; May 27, 1983; April 13, 1984; July 14, 1988; November 12, 1990; November 13, 1990.

Replaces E71747 dated July 8, 1991.

128651018

Underwriters Laboratories Inc.®

011/0044987