


5

4

3





2

1



vorverrastet
pre assembled
preassemble

verrastet
fitted
assemble



1) Markierung erster Kontakt, Ader 2 des Flachkabels
1) Contact no.1, 1st wire of flat cable
1) Contact no.1, repère 1 du câble

B

C

D

A



All Dimensions in mm
Original Size DIN A 4

Techn. Character.

Nicht tolerierte Masse/ Free size tolerances

09185105803

0,76 μm Au

09185106803

2

09185107803

3

Bestell-Nr.
Part-No.
Reference

Anforderungsstufe
performance level
Niveau de qualite

27570

01-FEB-00

JB

Mod.

Dat.

Name

HARTING EURL
F-95972 Paris



Detail.

01-FEB-00

Th

Insp.

01-FEB-00

JMV

Stand.

Massstab/Scale

2:1

SEK 18 Female connector
10 poles
with central polarisation
cover without cable stop

TB

0918510X803

Sub.

Blatt/ page

1/1