



NEW JOJO BASICS CABLE REELS

strength, safety and value

FEBRUARY 2004

JOJO are the world's leading manufacturers of cable reels. All JOJO reels are made and tested to the highest standards, being individually flash tested at 4000V, complying with the cable reels standard EN61242.

The **STRENGTH** and **SAFETY** characteristics of the designs ensures that these reels are suitable for daily, rigorous use, for a wide variety of applications including power tools, vacuum cleaners, lighting and

most other types of electrical appliances.

A heavy-duty range of 110V reels is available for use 'on site' - ideal for contractors and maintenance engineers using 110V power tools with industrial circular BS4343 power connectors.

All 240V reels have BS1363 plugs and sockets and are **Kitemark approved**. All JOJO reels benefit from the **JOJO Lifetime Guarantee**. Please visit <http://rswww.com/jojo> for more details.

JOJO 2 & 4 SOCKET CASSETTE REELS

Meets BS6500 BS1363 EN61242

- compact cassette type reels featuring moulded hand grip and integral plastic knob to ensure easy wind in and out action
- robust polypropylene construction
- current = 10Amp unbound

5 Metre 2 Socket Reel
Cable PVC 1.0mm² black
470-7985LX

10 Metre 2 Socket Reel
Cable PVC 1.0mm² black
470-8001LX

15 Metre 4 Socket Reel
Cable PVC 1.0mm² black
470-8023LX

JOJO 2 SOCKET OPEN REELS

Meets BS6500 BS1363 EN61242

LIFETIME QUALITY ASSURED GUARANTEE

- open reels featuring metallic stand and handgrip, with integral plastic knob to ensure easy wind in and out action
- current = 13Amp unbound

20 Metre 2 Socket Reel
Cable PVC 1.25mm² black
470-8017LX

25 Metre 2 Socket Reel
Cable PVC 1.25mm² black
470-8045LX

30 Metre 2 Socket Reel
Cable PVC 1.25mm² black
470-8051LX

40 Metre 2 Socket Reel
Cable PVC 1.25mm² black
470-8067LX

50 Metre 2 Socket Reel
Cable PVC 1.5mm² black
470-8073LX

JOJO 2 SOCKET 110V REELS

Meets EN60309 BS4343 EN61242

LIFETIME QUALITY ASSURED GUARANTEE

- designed with the contractor and maintenance engineer in mind
- for use on site on safety low voltage 110V power circuits
- ideal for local power distribution to 110V power tools and portable equipment
- yellow PVC cable
- tough polycarbonate BS 4343 IP44 rated industrial circular plug and sockets
- current = 16Amp unbound

20 Metre 2 Socket Reel 110V Semi-enclosed
Cable Arctic PVC 1.5mm² yellow
470-8152LX

25 Metre 2 Socket Reel 110V Open
Cable Arctic PVC 1.5mm² yellow
470-8089LX

40 Metre 2 Socket Reel 110V Open
Cable Arctic PVC 2.5mm² yellow
470-7991LX



NEW JOJO PREMIER CABLE REELS with thermal cut-out for added safety

The JOJO PREMIER range features all the strength and safety specifications of the JOJO BASICS range, but with the additional safety feature of an integral, resettable safety thermal cut-out to protect the reel against overloading and overheating. In the event of an overload, the cut-out trips to terminate the power to the connected appliances. Simply disconnect the appliances, press the reset button and check the appliance current rating before

reconnecting. **Don't forget, the current rating of the cable reel is significantly reduced when fully wound. Full current rating is achieved when fully unwound.**

An RCD version is available to provide 30mA earth leakage user protection against electric shock, for use outdoors or in situations where added shock protection is required.

Please visit <http://rswww.com/jojo> for more details.

JOJO 4 SOCKET CASSETTE REELS WITH CUT-OUT

Meets BS6500, BS1363, EN61242

LIFETIME QUALITY ASSURED GUARANTEE



- compact cassette type reels featuring moulded hand grip and integral plastic knob to ensure easy wind in and out action
- robust polypropylene construction for high impact resistance
- thermal cut-out

5 Metre 4 Socket Reel with Thermal Cut-Out
Current 13 Amp unwound
Cable PVC 1.25mm² black
470-8095LX

10 Metre 4 Socket Reel with Thermal Cut-Out
Current 13 Amp unwound
Cable PVC 1.25mm² black
470-8118LX

15 Metre 4 Socket Reel with Thermal Cut-Out
Current 10 Amp unwound
Cable PVC 1.0mm² black
470-8130LX

European 10 Metre 4 Socket Reel with Thermal Cut-Out and Schuko Connections to EN60884
Current 16 Amp unwound
Cable PVC 1.5mm² black
470-8124LX

JOJO 4 SOCKET OPEN REELS WITH CUT-OUT

Meets BS6500, BS1363, EN61242

LIFETIME QUALITY ASSURED GUARANTEE



- open reels featuring metallic stand and handgrip, with integral plastic knob to ensure easy wind in and out action
- robust polypropylene drum construction for high impact resistance
- thermal cut-out

25 Metre 4 Socket Reel with Thermal Cut-Out
Current 13 Amp unwound
Cable PVC 1.25mm² black
470-8174LX

40 Metre 4 Socket Reel with Thermal Cut-Out
Current 13 Amp unwound
Cable PVC 1.25mm² black
470-8203LX


50 Metre 4 Socket Reel with Thermal Cut-Out
Current 13 Amp unwound
Cable PVC 1.5mm² black
470-8219LX

European 40 Metre 4 Socket Reel with Thermal Cut-Out and Schuko Connections to EN60884
Current 16 Amp unwound
Cable PVC 1.5mm² black
470-8247LX

JOJO 4 SOCKET SEMI-ENCLOSED REELS + CUT-OUT

Meets BS6500, BS1363, BS7071, EN61242

LIFETIME QUALITY ASSURED GUARANTEE



- standing semi-enclosed cable reels featuring handgrip, with integral plastic knob to ensure easy wind in and out action
- robust polypropylene construction for high impact resistance
- thermal cut-out
- RCD version provided 30mA protection against electrical shock to BS7071

20 Metre 4 Socket Reel with Thermal Cut-Out
Current 13 Amp unwound
Cable PVC 1.25mm² black
470-8146LX

30 Metre 4 Socket Reel with Thermal Cut-Out
Current 13 Amp unwound
Cable PVC 1.25mm² black
470-8225LX

30 Metre 4 Socket Reel with RCD Cut-Out Plug
Current 13 Amp unwound
Cable PVC 1.25mm² orange
470-8231LX

European 25 Metre 4 Socket Reel with Thermal Cut-Out and Schuko Connections to EN60884
Current 16 Amp unwound
Cable PVC 1.25mm² black
470-8168LX

Terms and Conditions: All products in this issue are sold subject to the full conditions of sale set out in the current RS Catalogue, including conditions of price. Prices are valid at time of print but may be changed by RS at any time and exclude VAT which will be charged at the current rate. This issue is valid until 29th February 2004.