


Electrical & Pneumatic Lockout Devices



Non Conductive Lockouts

These orange nylon lockouts are 25.4 mm x 63.5 mm and allow the use of 6 padlocks. The lightweight (only 28 g) lockouts are easily carried from one location to another. The bright fluorescent orange colour makes it easy to recognise the lockout from a distance.

It locks out any piece of equipment safely and effectively.

Hole diameter: 9 mm.

Packaging: 1 piece



Part No.	Description
236916	Non Conductive Lockout

Scissor-Lok™ Lockout Device

A versatile and easy to use system for locking out multiple power sources and equipment.

This device can be used in conjunction with any lock with a shackle clearance of 19.05 mm. This unique lockout device can also secure power cords, freestanding equipment, tanks, cylinder of safety guards. The lock itself is made of heavy-duty chemical resistant nylon and is supplied with either 0.91 m or 3.04 m vinyl coated steel cable. If you choose to use your own cable, the outside diameter must be 4.76 mm or less.

Packaging: 1 piece

Part No.	Description
236921	Scissor Lok - 914 mm
236922	Scissor Lok - 3 m



Pneumatic Lockout/Tagout

Isolate pneumatic energy without the expense and inconvenience of installing in-line lockout valves. Brady's quick disconnect lockout is applied to the male fitting, isolating equipment from all compressed air sources. With a "glove fit," the lockout meets OSHA standards and accommodates the majority of 6.35 mm (1/4") 9.52 mm (3/8") and 12.7 mm (1/2") male fittings.

The center of the device allows for permanent storage on an air hose and a loop on the side can be used to hang the hose and lockout device. A padlock with 6.35 mm or 6.8 mm shackle diameter is required.

Packaging: 1 piece

Part No.	Description
064221	Pneumatic Lockout



Plug-Safe™ - Electrical Plug Lockout

- Safe and effective method for locking out electrical plugs
- Made of durable chemically resistant plastic
- Adjusts to lock out a variety of plug sizes
- Ability to lock out a plug up to 7 cm wide and 15 cm long with a maximum cord diameter of 3 cm.
- Accepts standard locks up to 1 cm shackle diameter

Packaging: 1 piece.

Part No.	Description	Size
065566	Plug-Safe™	15 cm long – 9 cm diameter

