

### Cold cathode (CCFL)/ Inverter selection Guide

P/N:	Description	Start Up Voltage required Vrms	BXA-12529 12V Dual Output-1000 Vrms <i>Fixed</i>	BXA-12576 12V Dual Output-800 Vrms <i>Fixed</i>	BXA-12579 12V Dual Output-1500 Vrms <i>Dimming</i>	BXA-12617C-6M 12V Dual Output-1200 Vrms <i>Dimming</i>	BXA-12553 12V Single Output-800 Vrms <i>Fixed</i>
			S/N 535-0041	S/N 535-0057	S/N 535-0063	S/N 535-0079	S/N 535-0085
BF20218-24B	2.0mm X 218mm	1250			√	√	
BF20226-24B	2.0mm X 226mm	1275			√	√	
BF20292-24B	2.0mm X 292mm	1650			Consult with JKL	Consult with JKL	
BF20325-24B	2.0mm X 325mm	1830			Consult with JKL		
BF22140-24B	2.2mm X 140mm	990	√	Consult with JKL	√	√	√
BF22258-25B	2.2mm X 258mm	1600			√	Consult with JKL	
BF26188-20B	2.6mm X 188mm	1115	√		√	√	Consult with JKL
BF26214-24B	2.6mm X 214mm	1450			√	Consult with JKL	
BF26240-24B	2.6mm X 240mm	1290			√	√	
BF26250-24B	2.6mm X 250mm	1350			√	Consult with JKL	
BF26285-20B	2.6mm X 285mm	1525			√	Consult with JKL	
BF26318-20B	2.6mm X 318mm	1710			√	Consult with JKL	
BF350-20B	3.2mm X 50mm	425	√	√	√	√	√
BF3100-20B	3.2mm X 100mm	640	√	√	√	√	√
BF3228-21B	3.2mm X 228mm	1190	√	Consult with JKL	√	√	√
BF3300-20B	3.2mm X 300mm	1625			Consult with JKL	Consult with JKL	
BF3380-20B	3.2mm X 380mm	1975			Consult with JKL		
BF3100-UV1	3.0mm X 100mm	650	√	√	√	√	√
BF959-UV1/3	9.0mm X 59mm	450	√	√	√	√	√

<b>BXA-502 5V Single Output- 800 Vrms Fixed</b>	<b>BXA-24529 24V Dual Output- 1000 Vrms Fixed</b>	<b>BXA-12563 12V Single Output- 1000 Vrms Dimming</b>	<b>BXA-503 6V Single Output- 1200 Vrms Fixed</b>
S/N 535-0091	S/N 535-0108	S/N 535-0114	S/N 535-0120
		√	√
		√	√
			Consult with JKL
√	√	√	√
			Consult with JKL
Consult with JKL	√	√	√
			Consult with JKL
		Consult with JKL	√
		Consult with JKL	Consult with JKL
			Consult with JKL
√	√	√	√
√	√	√	√
√	√	√	√
			Consult with JKL
√	√	√	√
√	√	√	√