

STYLE #	LINER MATERIAL	COATING MATERIAL	GRIP DESIGN	CUFF STYLE	THICKNESS MM	POWDER-FREE	AQL	COLOUR	EN SIZE	LENGTH MM	PACKAGING
25-101	N/A	Neoprene	Textured fingertips	Rolled beaded	0.13	Yes	1.5	Bright green	6½-7, 7½-8, 8½-9, 9½-10	240	100 gloves in a box, 10 boxes in a carton
25-201	N/A	Neoprene	Textured fingertips	Rolled beaded	0.13	Yes	1.5	Bright green	6½-7, 7½-8, 8½-9, 9½-10	285	100 gloves in a box, 10 boxes in a carton



## A unique combination of allergy prevention and comfort.

### PRIMARY INDUSTRIES



### IDEAL APPLICATIONS

- Handling, assembling and controlling applications in all types of industrial environments where there is no need for mechanical protection
- Lab work and analyses, especially when resistance to acids is required
- Pharmaceuticals

### DESCRIPTION

- The NeoTouch® gloves were the first neoprene single-use gloves for industrial usage.
- With a latex-free formulation, NeoTouch® gloves are appropriate for the prevention of Type I allergies. Because they're powder-free, they also limit the risk of dermatitis for the wearer.
- They provide excellent resistance to acids, bases and alcohols. Thanks to an exclusive formulation, NeoTouch® gloves are convincingly the most comfortable synthetic single-use gloves available today.
- NeoTouch® gloves have a polyurethane inner-coating that ensures easy donning. Their textured fingertips provide a secure grip in both dry and wet conditions. The beaded cuff ensures a secure hold, and their green colour makes them easy to identify.
- NeoTouch® gloves are inspected to an AQL of 1.5 for pinholes, which matches the legal requirements for medical gloves.

### REMARKS

- 25-101: Fit for special purpose



CATEGORY III

Print date: 08-05-2014

**Ansell Healthcare Europe N.V. (European Head Office)**

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

http://www.ansell.eu • E-mail info@ansell.eu