

## Product Information

### FTP125x40-Ø20 NL50

EAN 4031582331745

Wheel centre made of cast iron, Tread:  
Polyurethane, casted, precision ball bearing

|                   |                |
|-------------------|----------------|
| Wheel diameter    | 125 mm         |
| Width of Tread    | 40 mm          |
| Axle Hole Ø       | 20 mm          |
| Hub length        | 50 mm          |
| Temperature       | - 20 / + 60 °C |
| Standard          | EN 12533       |
| Hardness of tread | A 92 Shore     |

