

Customer Information Sheet

DRAWING No.: M80-9180099 - M80-9250099 SHEET 2 OF 2


IF IN DOUBT - ASK

©

NOT TO SCALE

THIRD ANGLE PROJECTION

ALL DIMENSIONS IN mm



SPECIFICATION:

MATERIAL:

CONTACT SHELL = BRASS
CONTACT CLIP = BERYLLIUM COPPER

FINISH:

CONTACT SHELL = 0.28µ GOLD
CONTACT CLIP = 0.3µ GOLD

PART No.	CRIMP CONTACT	AWG	DIM 'A'
M80-9180099	M80-0110005	22	150
M80-9190099	M80-0130005	24	150
M80-9200099	M80-0130005	26	150
M80-9210099	M80-0130005	28	150
M80-9220099	M80-0110005	22	300
M80-9230099	M80-0130005	24	300
M80-9240099	M80-0130005	26	300
M80-9250099	M80-0130005	28	300

NOTES:

- TO BE USED WITH CRIMP HOUSINGS M80-101XX98, M80-103XX98, M80-1485198, M80-1503098, M80-1522798, M80-1543698, M80-1564598, M80-1586398, M80-1600698, M80-1621598, M80-1642498, M80-1664298, M80-262XX98, M80-264XX98.
- WIRE & CRIMPS ARE ALL RoHS COMPLIANT

JMB	2	04.12.06	9600
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>JMB</i>			
CHECKED: <i>NSC</i>			
DRAWN: J. ENRIGHT			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

THIS DRAWING AND ANY INFORMATION OR DESCRIPTIVE MATTER SET OUT HEREON ARE CONFIDENTIAL AND COPYRIGHT PROPERTY OF THE HARWIN GROUP AND MUST NOT BE DISCLOSED, LOANED, COPIED OR USED FOR MANUFACTURING, TENDERING OR FOR ANY OTHER PURPOSE WITHOUT THEIR WRITTEN PERMISSION.

TOLERANCES

X. = ±1mm
X.X = ±0.25mm
X.XX = ±0.10mm
X.XXX = ±0.01mm
ANGLES = ±5°
UNLESS STATED

MATERIAL:

SEE ABOVE

FINISH: SEE ABOVE

S/AREA:

mm²

TITLE:

PRE-CRIMPED CONTACT
(M80-0110005 / M80-0130005)

DRAWING NUMBER:

M80-9180099 - M80-9250099

SHT
2
OF
2

HARWIN INC
U.S.A.

TEL: (812) 542 2540
FAX: (812) 542 2541

HARWIN PLC
U.K.

TEL: 023 9231 4545
FAX: 023 9231 4590

HARWIN PTE
SINGAPORE

TEL: 65 6779 4909
FAX: 65 6779 3868