



NEW EXTREME IMPACT RANGE



IMPACT HOLESAWS

IMPACT DRILLING



IMPACT SCREW DRIVING & ADAPTOR

IMPACT SOCKETS



COMPLETE IMPACT SOLUTION

GUARANTEED TOUGH.

IMPACT SCREWDRIVING RANGE

CAT NO.	DESCRIPTION	PACK QTY		
DT7381-QZ	25mm Torx Impact SDB T20	5		
DT7382-QZ	25mm Torx Impact SDB T25	5		
DT7384-QZ	25mm Torx Impact SDB T30	5		
DT7386-QZ	25mm Impact SDB Pz1	5		
DT7387-QZ	25mm Impact SDB Pz2	5		
DT7388-QZ	25mm Impact SDB Pz3	5		
DT7390-QZ	50mm Impact SDB Pz1	5		
DT7391-QZ	50mm Impact SDB Pz2	5		
DT7392-QZ	50mm Impact SDB Pz3	5		
DT7993-QZ	25mm Impact SDB Ph1	5		
DT7994-QZ	25mm Impact SDB Ph2	5		
DT7995-QZ	25mm Impact SDB Ph3	5		
DT7997-QZ	50mm Impact SDB Ph1	5		
DT7998-QZ	50mm Impact SDB Ph2	5		
DT7999-QZ	50mm Impact SDB Ph3	5		

Durable hex shank, fits all impact drivers

Single piece unit for increased durability

Full hex body design for increased strength and life

Optimised tip design, reduces camout



GUARANTEED TOUGH.

IMPACT HOLE SAWS

Ejection spring
Allows for ease of use
with no plug removal

Thin walled Design
Optimized for metal drill
efficiency

Raised Shoulder
Prevents over drilling
and breakthrough



CAT NO.	DESCRIPTION		
DT8253-QZ	Impact Rated Hole Saw - 19mm		
DT8254-QZ	Impact Rated Hole Saw - 22mm		
DT8255-QZ	Impact Rated Hole Saw - 25mm		
DT8256-QZ	Impact Rated Hole Saw - 29mm		
DT8257-QZ	Impact Rated Hole Saw - 32mm		
DT8258-QZ	Impact Rated Hole Saw - 35mm		
DT8259-QZ	Impact Rated Hole Saw - 38mm		

**Twice number of cuts of standard bi-metal hole saw in
sheet metal using impact tool**



IMPACT METAL DRILLING

CAT NO.	DESCRIPTION		
DT50600-QZ	Metal Impact Drill 3mm		
DT50602-QZ	Metal Impact Drill 3.5mm		
DT50603-QZ	Metal Impact Drill 4mm		
DT50605-QZ	Metal Impact Drill 4.5mm		
DT50607-QZ	Metal Impact Drill 5mm		
DT50608-QZ	Metal Impact Drill 5.5mm		
DT50609-QZ	Metal Impact Drill 6mm		
DT50611-QZ	Metal Impact Drill 7mm		
DT50613-QZ	Metal Impact Drill 8mm		
DT50616-QZ	Metal Impact Drill 10mm		
DT50617-QZ	Metal Impact Drill 11mm		
DT50618-QZ	Metal Impact Drill 12mm		
DT50619-QZ	Metal Impact Drill 13mm		

CAT NO.	DESCRIPTION		
DT70500B-QZ	Tough Case 3, 3.2, 3.5, 4, 4.5, 5, 6, 8, 10, 12mm (blister)		

Patented Pilot point tip – For increased speed, life and hole accuracy



Patented back tapered web – for increased durability

One Piece Integral Design – For increased durability, minimising bit breakage



MULTI MATERIAL BITS

CAT NO	SIZE	WORKING LENGTH		
DT6515-QZ	3mm	113mm		
DT6516-QZ	3.5mm	113mm		
DT6517-QZ	4mm	103mm		
DT6518-QZ	5mm	113mm		
DT6527-QZ	5.5mm	113mm		
DT6528-QZ	5.5mm	200mm		
DT6519-QZ	6mm	123mm		
DT6529-QZ	6mm	200mm		
DT6520-QZ	6.5mm	123mm		
DT6530-QZ	6.5mm	200mm		
DT6521-QZ	7mm	123mm		
DT6522-QZ	8mm	134mm		
DT6531-QZ	8mm	200mm		
DT6523-QZ	9mm	134mm		
DT6524-QZ	10mm	134mm		
DT6533-QZ	10mm	200mm		
DT6525-QZ	12mm	153mm		
DT6526-QZ	13mm	160mm		

APPLICATIONS

Suitable for wood, plastics, mild steel and non ferrous metal

For use in rotary or percussion drilling modes

**FEATURES**

Unique 120 degree tip grind for maximum sharpness

Fully supported carbide head gives faster drilling and extended life