



MODEL NAME : 9501 Rev. B

FRONT VIEW



Pin #	Assignment
1	Right
2	Left
3	Top
4	Bottom

NOTES:

1. ITO GLASS THICKNESS : 1.60mm
2. OVERALL THICKNESS : 1.90±0.10mm
3. CONNECTOR AND PINOUT AS INDICATED
4. FRONT SURFACE : ANTI-GLARE HARDCOAT
5. LAYER TO LAYER ASSEMBLY TOLERANCE: ±0.50mm
6. TAIL TYPE : INTEGRAL PET FILM WITH AMP-C , GOLD-PLATED CONTACTS
7. OTHER SPEC : SEE APPROVED SHEET



B	MAY 19, 2005	CONTACTS, HOUSING & ITO PET MODIFY	ALEX
A	APR 12, 2001	DIMENSIONS MODIFY	ALEX
NO.	DATE	DESCRIPTION	CHK
REVISION			
CHIEF OF DESIGN	APPROVED	Alex	
ENGINEER	PROJECT NUMBER		
DRAWN BY	Denise	DATE	OCT 11, 2007
SHT 1 OF 1	REV.	B	

Apex Material Technology Corp.

TOLERANCES UNLESS SPECIFIED		MODEL NAME :
.X	± 0.50	9501
.XX	± 0.25	DWG NO : 9501-2-012
.XXX	± 0.10	SCALE: 1:1 UNIT: mm
ANGULAR		