

Altistart ATS 22



NEW



The Altistart 22 is a range three phase Softstarters with built-in bypass. The ATS22 is a simple to use three phase digital softstart with embedded bypass function for a wide range of applications.

Complete with adjustable electronic overload and fieldbus communications.

- Compact size
- Simple connection
- Easy to commission
- Built-in bypass
- 3 programmable logic inputs
- 1 PTC input
- 2 relay output
- Motor thermal protection
- Overvoltage protection

Comparison Table

Description	Current Rating	Power rating	Height	Width	Depth	Stock No.
ATS22 17A 400V	17A	4-7,5 kW	265	130	169	7106363
ATS22 32A 400V	32A	7,5-15 kW	265	130	169	7106372
ATS22 47A 400V	47A	11-22 kW	265	130	169	7106388
ATS22 62A 400V	62A	15-30 kW	295	145	207	7106394
ATS22 75A 400V	75A	18,5-37 kW	295	145	207	7106405
ATS22 88A 400V	88A	22-45 kW	295	145	207	7106411
ATS22 110A 400V	110A	30-55 kW	356	150	229	7106427
ATS22 140A 400V	140A	37-75 kW	356	150	229	7106433
ATS22 170A 400V	170A	45-90 kW	356	150	229	7106458
ATS22 210A 400V	210A	55-110 kW	425	206	299	7106451
ATS22 250A 400V	250A	75-132 kW	425	206	299	7106455
ATS22 320A 400V	320A	90-160 kW	425	206	299	7106464
ATS22 410A 400V	410A	110-120 kW	455	304	340	7106467
ATS22 480A 400V	480A	132-250 kW	455	304	340	7106461
ATS22 590A 400V	590A	160-355 kW	455	304	340	7106470

Technical Specification

Phase Three
Voltage 230 -440V AC

Description	MPN	Stock No.	Price Per	£
ATS22 17A 400V	ATS22D17Q	7106363		
ATS22 32A 400V	ATS22D32Q	7106372		
ATS22 47A 400V	ATS22D47Q	7106388		
ATS22 62A 400V	ATS22D62Q	7106394		
ATS22 75A 400V	ATS22D75Q	7106405		
ATS22 88A 400V	ATS22D88Q	7106411		
ATS22 110A 400V	ATS22C11Q	7106427		
ATS22 140A 400V	ATS22C14Q	7106433		
ATS22 170A 400V	ATS22C17Q	7106458		
ATS22 210A 400V	ATS22C21Q	7106451		
ATS22 250A 400V	ATS22C25Q	7106455		
ATS22 320A 400V	ATS22C32Q	7106464		
ATS22 410A 400V	ATS22C41Q	7106467		
ATS22 480A 400V	ATS22C48Q	7106461		
ATS22 590A 400V	ATS22C59Q	7106470		