



**Ball joint, K8167S**

Ball joint with 1/2" drive.  
1/2" DIN 3121-G 12,5, ISO 1174.

**Finish:** forged, phosphated.

**Material:** VANADIUM-EXTRA.

Maximum angle 30°. With through hole.



K8167S

1237592

1

1/2"

1/2"

62

34 K560F-5 205