

## Angle measurement, cruciform, string and pipe spirit levels

### Type AWM Angle measurer



- Determine angles comfortably and precisely, even in difficult places, and read them easily and precisely from the unit's analogue display. The type AWM angle measurer makes this easy.
- The large locking screw enables any position to be set and horizontals and verticals to be checked via the built-in vials.

#### **Angle measurer AWM 37 cm:**

- Light metal rectangular profile angle measurer (37 cm) with 1 horizontal vial and 1 vertical vial.
- Measurement range 180°, readability 0.5°.

#### **Angle measurer AWM 60 cm:**

- Light metal rectangular profile angle measurer (60 cm) with 1 horizontal vial, 1 vertical vial and 2 compass points.
- The compass points can be replaced with pencils.
- Measurement range 180°, readability 0.5°.

### 2D level



Cross-shaped spirit level for aligning two horizontal levels simultaneously.

**Art.No** 07804/1