



# Sets

[Back](#)

# Robust, compact and easy to handle



**The handy Robust Line sets from Bosch** offer accessories for most applications in interior fitting work and on the construction site. The range comprises user-oriented sets with drill bits, diamond drill bits, jigsaw blades and screwdriver bits.

The compact Robust Line sets from Bosch excel due to their particularly robust and user-friendly design. The contents are clearly visible, the practical sets are easy to open and the accessories are easy to remove. The innovative shock-absorbing outer frame of the boxes withstands the biggest impact.

The Robust Line sets are ideal for machine or tool cases, but they also fit in your pocket. The required accessory is always quickly within reach and ready for use. With this, Bosch offers an effective solution for many applications.



**Robust and durable:** innovative shock-absorbing outer frame withstands the biggest impact



**Compact and always ready to hand:** handy and practical pocket-size design, within reach and ready for use at all times, contents can be seen at a glance



**Practical flip mechanism:** guarantees quick and easy removal and storage of the accessories



# Metal drill bit sets

## Metal drill bit sets HSS-R (rolled), DIN 338

Product properties	Ordering information	Diameter mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
--------------------	----------------------	-------------	-------------	----------------	---------------	------------------------	--------------------	----------------	-------------------



10-piece metal drill bit set HSS-R, DIN 338

1.0	1 609 200 203	P1k	10	1	004244	GAZ	15.85
2.0							
3.0							
4.0							
5.0							
6.0							
7.0							
8.0							
9.0							
10.0							



13-piece metal drill bit set HSS-R, DIN 338

1.5	1 609 200 201	P1k	13	1	004220	GAZ	13.25
2.0							
2.5							
3.0							
3.2							
3.5							
4.0							
4.5							
4.8							
5.0							
5.5							
6.0							
6.5							
1/16"	2 607 018 353	P1k	13	1	061094	GAZ	11.24
5/64"							
3/32"							
27/64"							
1/8"							
9/64"							
5/32"							
11/64"							
3/16"							
13/64"							
7/32"							
15/64"							
1/4"							

19-piece metal drill bit set HSS-R, DIN 338

1.0	2 607 018 354	M1a	19	1	061100	GAZ	30.55
1.5							
2.0							
2.5							
3.0							
3.5							
4.0							
4.5							
5.0							
5.5							
6.0							
6.5							
7.0							
7.5							
8.0							
8.5							
9.0							
9.5							
10.0							





### Metal drill bit sets HSS-R (rolled), DIN 338

Product properties		Ordering information							
		Diameter mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat

19-piece metal drill bit set HSS-R, DIN 338



1.0	2 607 018 355	P1k	19	1	061117	GAZ	26.45
1.5							
2.0							
2.5							
3.0							
3.5							
4.0							
4.5							
5.0							
5.5							
6.0							
6.5							
7.0							
7.5							
8.0							
8.5							
9.0							
9.5							
10.0							

25-piece metal drill bit set HSS-R, DIN 338



1.0	2 607 018 725	M1a	25	1	145886	GAZ	62.36
1.5							
2.0							
2.5							
3.0							
3.5							
4.0							
4.5							
5.0							
5.5							
6.0							
6.5							
7.0							
7.5							
8.0							
8.5							
9.0							
9.5							
10.0							
10.5							
11.0							
11.5							
12.0							
12.5							
13.0							



7-piece metal drill bit set HSS-R, DIN 338

2.0	2 607 017 036	P1k	7	4	557375	GAZ	13.70
3.0							
4.0							
5.0							
6.0							
8.0							
10.0							

**Robust Line metal drill bit sets HSS-G (ground), 135° drill bit tip**



Set size A:  
156.5 x 69.5 x 23 mm

Product properties		Ordering information							
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
6-piece Robust Line metal drill bit set HSS-G, DIN 338, 135°									
2.0	24	A	2 607 010 529	P1k	6	1	446136	GRL	8.35
3.0	33								
4.0	43								
5.0	52								
6.0	57								
8.0	75								



Set size B:  
156.5 x 106.5 x 23 mm

10-piece Robust Line metal drill bit set HSS-G, DIN 338, 135°									
1.0	12	B	2 607 010 535	P1k	10	1	446198	GRL	18.57
2.0	24								
3.0	33								
4.0	43								
5.0	52								
6.0	57								
7.0	69								
8.0	75								
9.0	81								
10.0	87								



Set size C:  
124.0 x 106.5 x 23 mm

13-piece Robust Line metal drill bit set HSS-G, DIN 338, 135°									
1.5	18	C	2 607 010 538	P1k	13	1	446228	GRL	14.86
2.0	24								
2.5	30								
3.0	33								
3.2	36								
3.5	39								
4.0	43								
4.5	47								
4.8	52								
5.0	52								
5.5	57								
6.0	57								
6.5	63								

**Metal drill bit sets, HSS-G (ground), DIN 338, 135° drill bit tip**



Product properties		Ordering information							
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
19-piece metal drill bit set HSS-G, DIN 338, 135°									
1.0			2 607 018 726	M1a	19	1	145893	GAZ	50.20
1.5									
2.0									
2.5									
3.0									
3.5									
4.0									
4.5									
5.0									
5.5									
6.0									
6.5									
7.0									
7.5									
8.0									
8.5									
9.0									
9.5									
10.0									



### Metal drill bit sets, HSS-G (ground), DIN 338, 135° drill bit tip

Product properties		Ordering information							
Diameter mm		Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
25-piece metal drill bit set HSS-G, DIN 338, 135°									
1.0		2 607 018 727	M1a	25	1	145909	GAZ	99.32	
1.5									
2.0									
2.5									
3.0									
3.5									
4.0									
4.5									
5.0									
5.5									
6.0									
6.5									
7.0									
7.5									
8.0									
8.5									
9.0									
9.5									
10.0									
10.5									
11.0									
11.5									
12.0									
12.5									
13.0									



### Robust Line metal drill bit sets HSS-G (ground), 118° drill bit tip

Product properties			Ordering information							
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
6-piece Robust Line metal drill bit set HSS-G, DIN 338, 118°										
2.0	24	A	2 607 010 528	P1k	6	1	446129	GRL	6.96	
3.0	33									
4.0	43									
5.0	52									
6.0	57									
8.0	75									
10-piece Robust Line metal drill bit set HSS-G, DIN 338, 118°										
1.0	12	B	2 607 010 534	P1k	10	1	446181	GRL	17.64	
2.0	24									
3.0	33									
4.0	43									
5.0	52									
6.0	57									
7.0	69									
8.0	75									
9.0	81									
10.0	87									



Set size A:  
156.5 x 69.5 x 23 mm



Set size B:  
156.5 x 106.5 x 23 mm

**Robust Line metal drill bit sets HSS-G (ground), 118° drill bit tip**



Set size C:  
124.0 x 106.5 x 23 mm

Product properties		Ordering information							
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
13-piece Robust Line metal drill bit set HSS-G, DIN 338, 118°									
1.5	18	C	2 607 010 537	P1k	13	1	446211	GRL	13.93
2.0	24								
2.5	30								
3.0	33								
3.2	36								
3.5	39								
4.0	43								
4.5	47								
4.8	52								
5.0	52								
5.5	57								
6.0	57								
6.5	63								

**Metal drill bit set HSS-G (ground), 118° drill bit tip**



Product properties		Ordering information							
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
19-piece metal drill bit set HSS-G, DIN 338, 118°									
1.0	18		2 607 018 361	P1k	19	1	061179	GAZ	47.87
1.5	24								
2.0	30								
2.5	33								
3.0	36								
3.5	39								
4.0	43								
4.5	47								
5.0	52								
5.5	57								
6.0	57								
6.5	63								
7.0	63								
7.5	63								
8.0	63								
8.5	63								
9.0	63								
9.5	63								
10.0	63								





**Robust Line metal drill bit sets HSS-TiN (titanium coating)**

Product properties		Ordering information								
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	



Set size A:  
156.5 x 69.5 x 23 mm

6-piece Robust Line metal drill bit set HSS-TiN, 135°

2.0	24	A	2 607 010 530	P1k	6	1	446143	GRL	28.80
3.0	33								
4.0	43								
5.0	52								
6.0	57								
8.0	75								



Set size B:  
156.5 x 106.5 x 23 mm

10-piece Robust Line metal drill bit set HSS-TiN, 135°

1.0	12	B	2 607 010 536	P1k	10	1	446204	GRL	65.03
2.0	24								
3.0	33								
4.0	43								
5.0	52								
6.0	57								
7.0	69								
8.0	75								
9.0	81								
10.0	87								



Set size C:  
124.0 x 106.5 x 23 mm

13-piece Robust Line metal drill bit set HSS-TiN, 135°

1.5	18	C	2 607 010 539	P1k	13	1	446235	GRL	54.82
2.0	24								
2.5	30								
3.0	33								
3.2	36								
3.5	39								
4.0	43								
4.5	47								
4.8	52								
5.0	52								
5.5	57								
6.0	57								
6.5	63								



### Spur auger bit sets, hex shank



Diameter mm		Working length mm		Total length mm		Part number		Packaging type		Pack quantity		Minimum order quantity		Barcode 3165140...		Discount group		List Price ex vat	
Product properties				Ordering information															
6-piece spur auger bit set																			
10	12	14	16	18	20	160	235	2 607 019 322	W0a	6	1	379090	GAZ	71.66					
10	12	14	16	18	20	360	450	2 607 019 323	W0a	6	1	379106	GAZ	176.28					

### Clean Hinge cutting bit set, tungsten carbide tipped



Diameter mm		Part number		Packaging type		Pack quantity		Minimum order quantity		Barcode 3165140...		Discount group		List Price ex vat	
Product properties				Ordering information											
5-piece Clean Hinge cutting bit set, tungsten carbide tipped															
15	20	25	30	35	2 607 017 008	W0a	1	1	536738	GAZ	203.27				

### Hinge cutting bit set, tungsten carbide tipped



5-piece tungsten carbide hinge cutting bit set															
15	20	25	30	35	2 607 018 750	W0a	5	1	148375	GAZ	96.43				

### Forstner drill bit set



5-piece Forstner drill bit set															
15	20	25	30	35	2 607 018 395	W0a	5	1	098120	GAZ	46.69				





### Concrete drill bit sets Silver Percussion

Product properties			Ordering information							
Diameter mm	Working length mm	Total length mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	



5-piece concrete drill bit set Silver Percussion

5.0	50	85	2 607 017 081	P1k	5	4	601351	GAZ	11.47
5.5	50	85							
6.0	60	100							
7.0	60	100							
8.0	80	120							



7-piece concrete drill bit set Silver Percussion

4.0	40	75	2 607 017 083	P1k	7	4	601375	GAZ	17.23
5.0	50	85							
5.5	50	85							
6.0	60	100							
7.0	60	100							
8.0	80	120							
10.0	80	120							

## Masonry drill bit sets

### Masonry drill bit sets Impact

Product properties			Ordering information							
Diameter mm	Working length mm	Total length mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	



7-piece masonry bit set Impact

3.0	30	60	2 607 017 035	P1k	7	4	557368	GAZ	12.20
4.0	40	75							
5.0	50	85							
5.5	50	85							
6.0	60	100							
7.0	60	100							
8.0	80	120							



# Mixed sets

## Sets for working in metal, wood, stone



Product properties			Ordering information							
Diameter, metal mm	Diameter, stone mm	Diameter, wood mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	

### 13-piece metal, wood, masonry bit set

2.0	4	4	2 607 018 367	P1k	13	1	061230	GAZ	14.15
2.5	5	5							
3.0	6	6							
4.0	8								
5.0									
6.0									



### 15-piece mixed drill bit set

3.0	3	3	2 607 017 038	P1k	15	1	557399	GAZ	23.77
4.0	4	4							
5.0	5	5							
6.0	6	6							
8.0	8	8							

# Multi-purpose drill bit sets

## Robust Line multi-purpose drill bit sets Multi Construction



Set size A:  
156.5 x 69.5 x 23 mm

Product properties		Ordering information								
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	

### 4-piece Robust Line multi-purpose drill bit set Multi Construction

5.5	50	A	2 607 010 522	P1k	4	1	446068	GRL	13.93
6.0	60								
7.0	60								
8.0	80								



Set size D:  
197.0 x 87.5 x 23 mm

### 7-piece Robust Line multi-purpose drill bit set Multi Construction

5.0	50	D	2 607 010 546	P1k	7	1	446303	GRL	26.01
5.5	50								
6.0	60								
6.0	60								
7.0	60								
8.0	80								
10.0	80								

## 5-piece tile drill bit sets Expert for Ceramic



Product properties		Ordering information								
Diameter mm	Working length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	

### 5-piece tile drill bit set Expert for Ceramic

4.0			2 608 587 169	P1k	5	1	599306	GAZ	33.07
5.0									
6.0									
8.0									
10.0									
5.5			2 608 587 170	P1k	5	1	599863	GAZ	35.37
6.0									
7.0									
8.0									
10.0									

\* Available from March 2011.



# Hammer drill bit sets

## Robust Line hammer drill bit sets X5L

Product properties				Ordering information						
Diameter mm	Working length mm	Total length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat

### 5-piece Robust Line hammer drill bit set X5L

5.5	100	165	D	2 607 019 930	P1k	5	1	517096	GRL	32.29
6.0	100	165	D	2 608 585 070	P1k	5	1	440370	GRL	29.45
7.0	100	165	D	2 607 019 931	P1k	5	1	517119	GRL	34.82
8.0	100	165	D	2 608 585 071	P1k	5	1	440387	GRL	32.41
10.0	100	165	D	2 608 585 072	P1k	5	1	440394	GRL	36.48
5.0	50	110	D	2 608 585 073	P1k	5	1	440400	GRL	30.70
6.0	50	115								
6.0	100	165								
8.0	100	165								
10.0	100	165								
5.5	100	165	D	2 607 019 933	P1k	5	1	517133	GRL	35.25
6.0	100	165								
7.0	100	165								
8.0	100	165								
10.0	100	165								
6.0	100	165	D	2 607 019 932	P1k	5	1	517126	GRL	35.60
6.0	100	165								
8.0	100	165								
8.0	100	165								
10.0	100	165								



Set size D:  
197.0 x 87.5 x 23 mm

## Robust Line hammer drill bit sets S4L

Product properties				Ordering information						
Diameter mm	Working length mm	Total length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat

### 5-piece Robust Line hammer drill bit set S4L

5.0	50	110	D	2 607 019 927	P1k	5	1	517072	GRL	21.24
6.0	50	110								
6.0	100	160								
8.0	100	160								
10.0	100	160								
5.5	100	160	D	2 607 019 929	P1k	5	1	517102	GRL	22.43
6.0	100	160								
7.0	100	160								
8.0	100	160								
10.0	100	160								
6.0	100	160	D	2 607 019 928	P1k	5	1	517089	GRL	22.81
6.0	100	160								
8.0	100	160								
8.0	100	160								
10.0	100	160								



Set size D:  
197.0 x 87.5 x 23 mm







# Holesaw sets

## Progressor holesaw sets

Product properties		Ordering information						
Diameter mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	



9-piece Progressor holesaw set  
6 holesaws, 1 Power Change adapter, 2 HSS-G pilot drill bits

20	2 608 584 670	U0	9	1	279901	GAQ	90.36
25							
32							
38							
51							
64							



14-piece Progressor holesaw set  
11 holesaws, 1 Power Change adapter, 2 HSS-G pilot drill bits

19	2 608 584 667	U0	14	1	279871	GAQ	167.98
22							
25							
29							
35							
38							
44							
51							
57							
64							
76							

## Sheet Metal holesaw sets



9-piece Sheet Metal set, plumber  
6 holesaws, 1 Power Change adapter, 2 HSS-Co pilot drill bits

19	2 608 584 813	U0	9	1	376341	GAQ	81.27
22							
29							
38							
44							
57							

9-piece Sheet Metal holesaw set, electrician  
6 holesaws, 1 Power Change adapter, 2 HSS-Co pilot drill bits

20	2 608 580 089	U0	9	1	464154	GAQ	75.55
25							
32							
38							
51							
64							





## Robust Line screwdriver bit sets, Max Grip version



Max Grip version  
Set size L1-2:  
122.0 x 65.0 x 21.5 mm

Product properties			Ordering information								
Set contents	Length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat		
18+1-piece Robust Line screwdriver bit set L, Max Grip version Bit length 25 mm, ISO 1173 C6.3, with quick change universal holder											
<ul style="list-style-type: none"> <li>⊕ PH1, PH2 (3x), PH3</li> <li>⊕ PZ1, PZ2 (3x), PZ3</li> <li>⊕ T8, T10, T15, T20, T25, T27, T30, T40 + QC UH</li> </ul>	25	L1	<b>2 607 002 581</b>	P1k	19	1	401647	GRL	37.12		
<ul style="list-style-type: none"> <li>⊕ PH1, PH2, PH3</li> <li>⊕ PZ1, PZ2, PZ3</li> <li>⊕ T10, T15, T20, T25, T30, T40</li> <li>● S0.6x4.5, S0.8x5.5, S1.2x8.0</li> <li>○ HEX4, HEX5, HEX6 + QC UH</li> </ul>	25	L2	<b>2 607 002 582</b>	P1k	19	1	401654	GRL	37.12		

## Robust Line screwdriver bit sets, Extra Hard version



Extra Hard version  
Set size Sx1-4:  
90.0 x 65.0 x 21.5 mm

8-piece Robust Line screwdriver bit set Sx, Extra Hard version Bit length 49 mm, ISO 1173 E6.3, without universal holder										
<ul style="list-style-type: none"> <li>⊕ PH1 (2x), PH2 (4x), PH3 (2x)</li> <li>⊕ PZ1 (2x), PZ2 (4x), PZ3 (2x)</li> </ul>	49	Sx1	<b>2 607 002 556</b>	P1k	8	1	401395	GRL	16.37	
<ul style="list-style-type: none"> <li>⊕ PH1, PH2 (2x), PH3</li> <li>⊕ PZ1, PZ2 (2x), PZ3</li> </ul>	49	Sx3	<b>2 607 002 558</b>	P1k	8	1	401418	GRL	16.37	
<ul style="list-style-type: none"> <li>⊕ T8, T10, T15, T20, T25, T27, T30, T40</li> </ul>	49	Sx4	<b>2 607 002 559</b>	P1k	8	1	401425	GRL	16.37	



Extra Hard version  
Set size S1-4:  
90.0 x 65.0 x 21.5 mm

8+1-piece Robust Line screwdriver bit set S, Extra Hard version Bit length 25 mm, ISO 1173 C6.3, with quick change universal holder										
<ul style="list-style-type: none"> <li>⊕ PH1 (2x), PH2 (4x), PH3 (2x) + QC UH</li> <li>⊕ PZ1 (2x), PZ2 (4x), PZ3 (2x) + QC UH</li> <li>⊕ T10, T15, T20 (2x), T25 (2x), T30, T40 + QC UH</li> </ul>	25	S1	<b>2 607 002 560</b>	P1k	9	1	401432	GRL	16.37	
<ul style="list-style-type: none"> <li>⊕ PZ1 (2x), PZ2 (4x), PZ3 (2x) + QC UH</li> </ul>	25	S2	<b>2 607 002 561</b>	P1k	9	1	401449	GRL	16.37	
<ul style="list-style-type: none"> <li>⊕ T10, T15, T20 (2x), T25 (2x), T30, T40 + QC UH</li> </ul>	25	S3	<b>2 607 002 562</b>	P1k	9	1	401456	GRL	16.37	



### Robust Line screwdriver bit sets, Extra Hard version

Product properties	Ordering information
--------------------	----------------------

12+1-piece Robust Line screwdriver bit set M, Extra Hard version  
 Bit length 25 mm, ISO 1173 C6.3, with quick change universal holder



Extra Hard version  
 Set size M1-4:  
 90.0 x 65.0 x 21.5 mm

Set contents	Length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
<ul style="list-style-type: none"> <li>⊕ PH1, PH2, PH3</li> <li>⊗ PZ1, PZ2, PZ3</li> <li>⊗ T10, T15, T20, T25, T30, T40 + QC UH</li> </ul>	25	M1	<b>2 607 002 563</b>	P1k	13	1	401463	GRL	21.02
<ul style="list-style-type: none"> <li>⊕ PH1 (2x), PH2 (3x), PH3</li> <li>⊗ PZ1 (2x), PZ2 (3x), PZ3 + QC UH</li> </ul>	25	M2	<b>2 607 002 564</b>	P1k	13	1	401470	GRL	21.02
<ul style="list-style-type: none"> <li>⊗ T8, T10, T15 (2x), T20 (2x), T25 (2x), T27, T30 (2x), T40 + QC UH</li> </ul>	25	M3	<b>2 607 002 565</b>	P1k	13	1	401487	GRL	21.02
<ul style="list-style-type: none"> <li>⊕ PH1, PH2, PH3</li> <li>⊗ PZ1, PZ2, PZ3</li> <li>⊗ T15, T20, T25</li> <li>⊖ S0.6x4.5, S0.8x5.5, S1.2x8.0 + QC UH</li> </ul>	25	M4	<b>2 607 002 566</b>	P1k	13	1	401494	GRL	21.02

18+1-piece Robust Line screwdriver bit set L, Extra Hard version  
 Bit length 25 mm, ISO 1173 C6.3, with quick change universal holder



Extra Hard version  
 Set size L1-3:  
 122.0 x 65.0 x 21.5 mm

Set contents	Length mm	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
<ul style="list-style-type: none"> <li>⊕ PH1, PH2 (3x), PH3</li> <li>⊗ PZ1, PZ2 (3x), PZ3</li> <li>⊗ T8, T10, T15, T20, T25, T27, T30, T40 + QC UH</li> </ul>	25	L1	<b>2 607 002 567</b>	P1k	19	1	401500	GRL	28.63
<ul style="list-style-type: none"> <li>⊕ PH1, PH2, PH3</li> <li>⊗ PZ1, PZ2, PZ3</li> <li>⊗ T10, T15, T20, T25, T30, T40</li> <li>⊖ S0.6x4.5, S0.8x5.5, S1.2x8.0</li> <li>⊖ HEX4, HEX5, HEX6 + QC UH</li> </ul>	25	L2	<b>2 607 002 568</b>	P1k	19	1	401517	GRL	28.63
<ul style="list-style-type: none"> <li>⊗ Th7, Th8, Th9, Th10, Th15, Th20, Th25, Th27, Th30, Th40</li> <li>⊗ TW1, TW2, TW3, TW4</li> <li>⊗ SP6, SP8, SP10</li> <li>⊖ R2 + QC UH</li> </ul>	25	L3	<b>2 607 002 569</b>	P1k	19	1	401524	GRL	37.12





## Screwdriver bit set





Product properties	Ordering information							
Set contents	Length mm	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat
25-piece screwdriver bit set								
PH1, PH2 (2x), PH3	25	2 607 017 037	P1k	25	1	557382	GAZ	24.00
PZ1, PZ2 (2x), PZ3	25							
T10, T15, T20 (2x), T25, T27, T30, T40	25							
PH2	49							
PZ2	49							
T10, T15, T20, T25, T30, T40 + UH	49							


 Phillips (PH)


 Pozidriv (PZ)


 Torx® (T)


 Security Torx® (Th)

 Spanner (Sp)

 Slotted screw (S)

 Internal hexagon (HEX)

 Tri-Wing® (Tw)

 Internal square (R)

**UH** = Universal Holder

**QC UH** = Quick Change Universal Holder

Torx® is a registered trademark of Camcar Div., Textron Inc.

Tri-Wing® is a registered trademark of Phillips Screw Co.



# Jigsaw blade sets

## Robust Line jigsaw blade sets, single lug shank

Product properties		Ordering information							
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	



Set size A:  
157 x 70 x 23 mm

### 6-piece Robust Line jigsaw blade set Progressor

T 123 XF Progressor for Metal	A	<b>2 607 010 531</b>	P1k	2	1	446150	GRL	15.33	
T 234 X Progressor for Wood				2					
T 345 XF Progressor for Wood and Metal				2					

### 6-piece Robust Line jigsaw blade set Wood Expert

T 308 B Extraclean for Wood	A	<b>2 607 010 572</b>	P1k	1	1	475976	GRL	15.33	
T 308 BF Extraclean for Hard Wood				1					
T 301 BCP Precision for Wood				2					
T 234 X Progressor for Wood				2					

### 6-piece Robust Line jigsaw blade set Metal Profile

T 318 AF Flexible for Metal	A	<b>2 607 010 573</b>	P1k	2	1	475983	GRL	15.79	
T 318 BF Flexible for Metal				2					
T 345 XF Progressor for Wood and Metal				2					



Set size C:  
124 x 107 x 23 mm

### 10-piece Robust Line jigsaw blade set Wood Expert

T 101 AO Clean for Wood	C	<b>2 607 010 540</b>	P1k	1	1	446242	GRL	16.72	
T 101 B Clean for Wood				1					
T 101 BR Clean for Wood				1					
T 101 AOF Clean for Hard Wood				1					
T 101 BF Clean for Hard Wood				1					
T 101 BRF Clean for Hard Wood				1					
T 244 D Speed for Wood				1					
T 144 D Speed for Wood				1					
T 144 DF Speed for Hard Wood				1					
T 144 DP Precision for Wood				1					

### 10-piece Robust Line jigsaw blade set Metal Expert

T 118 G Basic for Metal	C	<b>2 607 010 541</b>	P1k	1	1	446259	GRL	18.57	
T 118 A Basic for Metal				1					
T 118 B Basic for Metal				1					
T 118 EOF Flexible for Metal				1					
T 118 AF Flexible for Metal				1					
T 118 BF Flexible for Metal				1					
T 118 GFS Basic for Inox				1					
T 227 D Special for Alu				1					
T 127 D Special for Alu				1					
T 123 XF Progressor for Metal				1					

### 10-piece Robust Line jigsaw blade set Wood and Metal

T 244 D Speed for Wood	C	<b>2 607 010 542</b>	P1k	1	1	446266	GRL	16.25	
T 144 D Speed for Wood				1					
T 101 AO Clean for Wood				1					
T 101 B Clean for Wood				1					
T 101 AOF Clean for Hard Wood				1					
T 101 BF Clean for Hard Wood				1					
T 118 EOF Flexible for Metal				1					
T 118 AF Flexible for Metal				1					
T 118 BF Flexible for Metal				1					
T 123 XF Progressor for Metal				1					

## Robust Line jigsaw blade sets, single lug shank



Set size C:  
124 x 107 x 23 mm

Product properties		Ordering information							
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
<b>10-piece Robust Line jigsaw blade set Top Expert</b>									
T 130 RIFF Special for Ceramics	C	<b>2 607 010 574</b>	P1k	1	1	475990	GRL	24.62	
T 118 AHM Special for Inox				1					
T 141 HM Special for Fiber and Plaster				1					
T 101 A Special for Acrylic				1					
T 113 A Special for Soft Material				1					
T 101 BF Clean for Hard Wood				1					
T 101 BIF Special for Laminate				1					
T 118 AF Flexible for Metal				1					
T 227 D Special for Alu				1					
T 123 XF Progressor for Metal				1					

## Robust Line jigsaw blade set, U-shank

### 6-piece Robust Line jigsaw blade set Progressor

Product properties	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
U 123 XF Progressor for Metal	A	<b>2 607 010 532</b>	P1k	2	1	446167	GRL	15.33	
U 234 X Progressor for Wood				2					
U 345 XF Progressor for Wood and Metal				2					

## 10-piece jigsaw blade sets, single lug shank



Product properties		Ordering information							
Set contents	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
<b>10-piece jigsaw blade set Wood Basic</b>									
T 119 B0 Basic for Wood		<b>2 607 010 629</b>	P1k	2	1	579353	GAZ	11.70	
T 119 B Basic for Wood				4					
T 111 C Basic for Wood				4					



### 10-piece jigsaw blade set Wood/Metal Basic

Product properties	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
T 119 B0 Basic for Wood		<b>2 607 010 630</b>	P1k	2	1	579360	GAZ	14.93	
T 119 B Basic for Wood				2					
T 111 C Basic for Wood				2					
T 218 A Basic for Metal				1					
T 118 G Basic for Metal				1					
T 118 A Basic for Metal				1					
T 118 B Basic for Metal				1					



### 10-piece jigsaw blade set Metal Basic

Product properties	Set size	Part number	Packaging type	Pack quantity	Minimum order quantity	Barcode 3165140...	Discount group	List Price ex vat	
T 218 A Basic for Metal		<b>2 607 010 631</b>	P1k	2	1	579377	GAZ	20.26	
T 118 G Basic for Metal				2					
T 118 A Basic for Metal				3					
T 118 B Basic for Metal				3					