

# VH AA 1700 CLG



## Specifications

Capacity	1700mAh
Chemistry	NiMH
Dimensions	49.9 x 13.9mm
Maximum Continuous Current	5.1mA
Maximum Operating Temperature	+40°C
Minimum Operating Temperature	0°C
Nominal Voltage	1.2V
Operating Temperature Range	0 → +40°C
Size	AA
Terminal Type	Standard

### VH Series Ni / MH rechargeable batteries with lugs

Ni/MH rechargeable batteries with lugs.

Higher capacity than Ni / Cd rechargeable batteries.

No memory effect.

Nominal voltage:	1.2 Vdc
Operating temperature under discharge:	-20 °C → +40 °C

Stock no.	Type	Format	Dim (mm) Ø x h	Capacity (mAh)
<a href="#">483-4403</a>	VH AAA CLG	AAA	10.5 x 44.9	600
<a href="#">218-4554</a>	VH 4 / 5 A CLG	4 / 5 A	16.9 x 43.2	1600
<a href="#">455-8749</a>	VH AA 1700 CLG	AA	14.4 x 50.7	1700
<a href="#">419-9772</a>	VH Cs 3000 CLG	Cs	22.2 x 42.2	3000
<a href="#">455-8777</a>	VH D 9500 CLG	D	32.2 x 60.3	9500