

SOLID P 303018 G



Order symbol: P 303018 G
Product nbr: 8855211
Description: Enclosure, Polyester
Remarks: Grey cover

EAN: 6418074064059
El. number:
Finland: 3438013
Denmark: 8212040025
Sweden: 8855211
Norway:

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Sample photo

Dimensions:		Length	Width	Height	Rating:
mm:		300	300	175	Ingress Protection (EN 60529): IP 67
inch:		11.8	11.8	6.9	Impact Resistance (EN 62262): IK 10
Materials:					Electrical insulation: Totally insulated
Material:		Polyester			Halogen free (DIN/VDE 0472, Part 815): Yes
Base colour:		RAL 7036			UV resistance: UL 508
Cover colour:		RAL 7036			Flammability Rating (UL 746 C 5): UL 746C 5V
Cover screws material:		Polyamide			Glow Wire Test (IEC 695-2-1) °C: 960
Cover screws colour:		Black			NEMA Class: NEMA 3, 3R, 4, 4X, 6, 6P, 12, 13
Gasket material:		PUR			
Temperatures:					Certificates:
Short term:		-50 ... 160 °C			Gost R
Continuous:		-40 ... 80 °C			
Short term:		-58 ... 320 °F			
Continuous:		-40 ... 176 °F			
Accessories:					
MP 3030		Mounting plate			
MPX 3030		Mounting plate			
MPS S3		Mounting set for mounting plates			
DRF 331		DIN rail frame			

P3030 Top view -cover removed

