

## Datasheet

Item No. 92.238.6060.2

### Cable assembly GST18I3K1BS 25H 60WS

Extension cable, female - male, length 6m, GST18i3, 3 pole, 250V/16A, cable type S05Z1Z1, halogen-free, cross section 2,5 mm<sup>2</sup>, color of coding: white, color of cable: white

Item No.	92.238.6060.2
EAN	4015573664654
order unit	10 Piece(s)

## Approvals

## Technical data

### General

Rated current	16 A
Rated voltage	250 V
Rated impulse voltage	4 kV
Pollution degree	2
Mechanical coding	Yes
Interlockable	Yes
Color of coding/ contact carrier	White
Color of housing inclusive strain relief	White

### Model

Number of poles	3
Nominal cross section conductor	2.5 mm <sup>2</sup>
Degree of protection (IP)	IP40
Cable type	H05Z1Z1-F
Cable colour	White
Cable diameter	10.2 mm
Version of cable	Female - male

### Material

Surface finish	Tin-plated
Halogen free	Yes
Continuous temperature of cable	70 °C
Insulation components continuous temperature	100 °C

### Dimensions

Total length	6 m
--------------	-----

## Accessories

Item. No.	Typ:	Description:
-----------	------	--------------

## Drawings