

DIN-Power E048MS-3,0C1-2 NFF



Image is for illustration purposes only.
Please refer to product description.

Part number:	09 05 148 6921 222
Description:	DIN-Power E048MS-3,0C1-2 NFF
Combination:	Backplane-to-Daughtercard Cable to Board
Termination length:	3.0 mm
usage on ...-side:	Daughtercard
No. of contacts:	48
Performance level:	PL 2 acc. to IEC 60603-2
pcb fixing:	without snap in clips
Quality-Level:	standard
Contact Pitch:	5.08 mm
Series:	DIN 41612
Current:	6 A @ 20°C
contact orientation:	angled
Gender:	Male
Plastic features:	CTI < 400
Railway classification:	F1/I2 acc. to NFF 16-101
Type:	E
Termination Type:	Solder
Flange:	with Flange
Mating face:	DIN type E
RoHS conformity:	Yes