

SYNTECH HUR100x36-Ø12 white

EAN 4031582400687

Hybrid-wheel "SYNTECH", wheel centre and tread made of Polyamide, with elastic solid rubber centre, noise reduced, roller bearing

Technical Data	
Wheel diameter	100 mm
Width of Tread	36 mm
Axle Hole-Ø	12 mm
Hub length	44 mm
Temperature	- 20 / + 60 °C
Standard	EN 12532
Weight	0.4 kg
Hardness of tread	D 75 Shore
Load capacity	160 kg
Load capacity (static)	320 kg



Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+

