



DC Compact Fan Kits

Kits incorporating a range of DC fans, a controller and either a metal guard or an air filter option.

- 12 & 24V fans
- Plastic fan housings
- IP20 Protection
- Lead 310mm
- Filter pads that can be changed without switching off the fan

Part Number	Airflow		Voltage	Noise	Bearings	Power	Speed	Temperature Range	Length	Width	Depth	Fan Type	Wire Guard	Filter	Controller
	M3/h	CFM	V	dB(A)		W	RPM	°C	mm	mm	mm				
8412NG-KR0	69	40.6	12	32	SB	2.0	3100	-20...+70	80	80	25	8412NG	LZ22K	-	CDC122055UC-R
8412NG-KR1	69	40.6	12	32	SB	2.0	3100	-20...+70	80	80	25	8412NG	-	PMFA80	CDC122055UC-R
8412NGH-KR0	79	46.5	12	37	SB	2.8	3600	-20...+70	80	80	25	8412NGH	LZ22K	-	CDC122055UC-R
8412NGH-KR1	79	46.5	12	37	SB	2.8	3600	-20...+70	80	80	25	8412NGH	-	PMFA80	CDC122055UC-R
8414NG-KR0	69	40.6	24	32	SB	2.0	3100	-20...+70	80	80	25	8414NG	LZ22K	-	CDC242055UC-R
8414NG-KR1	69	40.6	24	32	SB	2.0	3100	-20...+70	80	80	25	8414NG	-	PMFA80	CDC242055UC-R
8414NGH-KR0	79	46.5	24	37	SB	2.8	3600	-20...+70	80	80	25	8414NGH	LZ22K	-	CDC242055UC-R
8414NGH-KR1	79	46.5	24	37	SB	2.8	3600	-20...+70	80	80	25	8414NGH	-	PMFA80	CDC242055UC-R
3412NHH-KR0	102	60	12	39	BB	2.9	3250	-20...+60	92	92	25	3412NHH	LZ23K	-	CDC122055UC-R
3412NHH-KR1	102	60	12	39	BB	2.9	3250	-20...+60	92	92	25	3412NHH	-	PMFA90	CDC122055UC-R
3414NHH-KR0	102	60	24	39	BB	2.7	3250	-20...+70	92	92	25	3414NHH	LZ23K	-	CDC242055UC-R
3414NHH-KR1	102	60	24	39	BB	2.7	3250	-20...+70	92	92	25	3414NHH	-	PMFA90	CDC242055UC-R
4412FM-KR0	140	82.4	12	38	BB	3.2	2400	-20...+75	119	119	25	4412FM	LZ30K	-	CDC122055UC-R
4412FM-KR1	140	82.4	12	38	BB	3.2	2400	-20...+75	119	119	25	4412FM	-	PMFA120	CDC122055UC-R
4414FM-KR0	140	82.4	24	38	BB	3.2	2400	-20...+75	119	119	25	4414FM	LZ30K	-	CDC242055UC-R
4414FM-KR1	140	82.4	24	38	BB	3.2	2400	-20...+75	119	119	25	4414FM	-	PMFA120	CDC242055UC-R
4312-KR0	170	100.1	12	45	BB	5.0	2800	-20...+75	119	119	32	4312	LZ30K	-	CDC122055UC-R
4312-KR1	170	100.1	12	45	BB	5.0	2800	-20...+75	119	119	32	4312	-	PMFA120	CDC122055UC-R
4314-KR0	170	100.1	24	45	BB	5.0	2800	-20...+75	119	119	32	4314	LZ30K	-	CDC242055UC-R
4314-KR1	170	100.1	24	45	BB	5.0	2800	-20...+75	119	119	32	4314	-	PMFA120	CDC24055UC-R