


## DIN rail perforated - NS 35/ 7,5 BLK PERF 2000MM - 0801759

Please be informed that the data shown in this PDF Document is generated from our Online Catalog. Please find the complete data in the user's documentation. Our General Terms of Use for Downloads are valid (<http://phoenixcontact.com/download>)




DIN rail, material: Steel, uncoated, perforated, height 7.5 mm, width 35 mm, length: 2 m

### Why buy this product

- If you require greater quantities, the same article is available in a unit pack of 25 pcs. (50 m)
- 



### Key commercial data

Packing unit	5 pc
Minimum order quantity	5 pc
GTIN	 4 017918 155438
Weight per Piece (excluding packing)	640.0 g
Custom tariff number	72166190
Country of origin	Germany

### Technical data

#### Dimensions

Height	7.5 mm
Length	2000 mm
Width	35 mm

#### General

Material	Steel
Coating	uncoated
Color	white aluminum
Test standard	In acc. with EN 60715: 2001
Nominal current I <sub>N</sub>	1920 A

## DIN rail perforated - NS 35/ 7,5 BLK PERF 2000MM - 0801759

### Classifications

#### eCl@ss

eCl@ss 4.0	27110804
eCl@ss 4.1	27110804
eCl@ss 5.0	27141143
eCl@ss 5.1	27141143
eCl@ss 6.0	27400602
eCl@ss 7.0	27400602
eCl@ss 8.0	27400602

#### ETIM

ETIM 2.0	EC001285
ETIM 3.0	EC001285
ETIM 4.0	EC000212
ETIM 5.0	EC000212

#### UNSPSC

UNSPSC 6.01	30212109
UNSPSC 7.0901	39121708
UNSPSC 11	39121708
UNSPSC 12.01	39121708
UNSPSC 13.2	39121708

### Drawings

# DIN rail perforated - NS 35/ 7,5 BLK PERF 2000MM - 0801759

Dimensional drawing

