











7000 Series torque wrenches with reversible ratchet



Design: Reversible ratchet, reading accuracy of $\pm 4\%$ of set value
Application: Can be used in right-hand direction; Article No. 7005 C with push-through square for both right and left-hand direction

									
Code	Art.No.		Nm	Nm	lbf. ft.	lbf. ft.	mm		
05075393001	7000 A	1/4"	1-25	0.10	1.5-18	0.10	290		RSStock Nr 7887047
05075394001	7000 B	3/8"	8-60	1	5-45	1,00	305		
05075400001	7000 C	1/2"	8-60	1	5-45	1,00	305		
05075405001	7001 B	3/8"	20-100	1	15-80	1,00	340		
05075401001	7001 C	1/2"	20-100	1	15-80	1,00	340		
05075402001	7003 C	1/2"	40-200	2	30-150	2,00	440		
05075415001 ¹⁾	7005 C	1/2"	60-300	5	45-220	5,00	570		
05075403001	7006 E	3/4"	80-400	10	60-295	10,00	685		

¹⁾ With push-through square. For both right and left direction