

CASES
1010
Micro Case

Save as PDF



Peli protector cases - Total protection boxes - Micro Case 1010



Interior dimensions:

11.1 x 7.3 x 4.3 cm (4" x 3" x 2")

GREAT FOR RUGGED SPORTS - NOT FOR SWIMMING OR SUBMERGING

Water resistant, crushproof, and dust proof. Not for swimming or diving.

Easy open latch

Rubber liner for extra protection doubles as o-ring seal

Stainless steel hardware

Lanyard

Unconditionally Guarantee of Excellence

Available in solid colour or clear with coloured liner



Micro_black Micro_blue Micro_red Micro_yellow

Peli protector cases - Total protection boxes - Micro Case 1010 SPECIFICATIONS

Exterior Dimensions (L x W x D)		Interior Dimensions (L x W x D)	
14.9 x 10.3 x 5.4 cm (6" x 4" x 2")		11.1 x 7.3 x 4.3 cm (4" x 3" x 2")	
Lid Depth	Bottom Depth	Total Depth	
1.8 cm (1")	2.4 cm (0.94")	4.1 cm (1.63")	
Lid Depth	Bottom Depth	Total Depth	
1.8 cm (0.69")	2.4 cm (0.94")	4.1 cm (1.63")	
Weight w/Foam	Weight w/o Foam	Buoyancy Max.	
0.19 kg. (0.41 lbs)	0.18kg (0.4 lbs.)	0.23 kg (0.51 lbs.)	
Range Temperature			
-23 / 93° C (-10 / 199.4° F)			

Materials

Body	Latch	Lid O-Ring	Pins
Polycarbonate	Xylex	Thermal Plastic Rubber Liner Stainless Steel	

Foam	Purge Body	Purge Vent	Purge O-Ring
TL - 426 4 lb. Esther	Polycarbonate	Polyester Spun- Bond ePTFE Oleophobic	70 Shore Nitrile

Configuration

Cat. #	Description
1010	Peli protector cases - Total protection boxes - Micro Case 1010

Peli protector cases - Total protection boxes - Micro Case 1010 Accessories

No accessories are currently available for this product

1010 Micro Case Certificates

- IP67(1 meter submersion for 30 minutes)