

MATERIALS AND FINISHES


SMA PLUG: (73251-4980)
SEE SD-73251-498

SMP JACK: (73406-6680)
SEE SD-73406-668

CABLE:
TEMP-FLEX 086-2201

LABEL:
BRADY PERMASLEEVE

SHRINK TUBE:
VERSAFIT OR EQUIVALENT



89762-1403	120.0	3048	10.0
89762-1402	12.00	304.8	1.45
89762-1401	9.00	228.6	1.07
89762-1400	6.00	152.4	0.70
PART NO.	IN	MM	MAX INSERTION LOSS TO 26 GHz (dB)
A			

MAX VSWR 1.50 @ 26 GHz

CHG: ADD MOLEX TO LABEL EC NO: URF2014-0398 DRWN: JWIENER 2014/01/03 CHKD: AZR 2014/01/03 APPR: JWIENER 2014/01/09 REV: A2	QUALITY SYMBOLS ▽=0 ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <tr> <td></td> <td>mm</td> <td>INCH</td> </tr> <tr> <td>4 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>3 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>2 PLACES</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>1 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> <tr> <td>0 PLACE</td> <td>± ---</td> <td>± ---</td> </tr> </table>		mm	INCH	4 PLACES	± ---	± ---	3 PLACES	± ---	± ---	2 PLACES	± ---	± ---	1 PLACE	± ---	± ---	0 PLACE	± ---	± ---	DIMENSION STYLE MM/IN DRAWN BY: JLEE02 DATE: 2013/03/27 CHECKED BY: SSS DATE: 2013/03/27 APPROVED BY: JWIENER DATE: 2013/11/22	SCALE DESIGN UNITS METRIC THIRD ANGLE PROJECTION	TITLE CA SMA P STR / SMP J STR TF086-2201 CABLE EWR-5133, CA-SMA/SMP molex
		mm	INCH																				
	4 PLACES	± ---	± ---																				
	3 PLACES	± ---	± ---																				
2 PLACES	± ---	± ---																					
1 PLACE	± ---	± ---																					
0 PLACE	± ---	± ---																					
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-89762-140	SHEET NO. 1 OF 1																			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																							