

Cable ties and document holders



For grouping together and organising audio, computer, VDI, etc., cables
Re-usable (cables can be added)

Pack	Cat.Nos	Cable ties with tightening indicator			
		Wide cable ties with patented warning system to prevent overtightening cables Release by pinching the head of the cable tie Strap held in place after tightening			
				Tightening \varnothing	
		Width (mm)	Length (mm)	max.	min.
50	0 331 94	15	180	35	15
50	0 331 95	15	225	50	35
50	0 331 96	15	320	80	50

Pack	Cat.Nos	Self-locking cable ties			
		Repositionable cable ties Double-sided textile with "loops" on one side and "hooks" on the other Do not damage cables Can be fixed using screws or rivets Cat.Nos 0 366 44/46 (p. 300)			
		Colour	Width (mm)	Length (mm)	Tightening \varnothing max. (mm)
10	0 331 84	Black	16	150	35
10	0 331 85	Red	16	150	35
10	0 331 86	Green	16	150	35
10	0 331 87	Black	16	300	80
10	0 331 88	Red	16	300	80
10	0 331 89	Green	16	300	80

Pack	Cat.Nos	Self adhesive base	
50	0 320 68	For cable ties max. width 20 mm Black - 38 x 38 x 9.4 mm Possible central fixing with screw \varnothing 4 mm	

Pack	Cat.Nos	Self-adhesive document holders				
		Open - RAL 7035				
		Ext. dimensions		Int. dimensions		
		Height (mm)	Width (mm)	Height (mm)	Width (mm)	Depth (mm)
20	0 365 80	235	340	200	310	18
20	0 365 81	165	260	130	230	18
		Closed - RAL 7035				
		Rigid plastic - IP 50 Int. dimensions: 324 x 120 x 18 mm				
1	0 365 82					
		Transparent				
10	0 097 99	Soft plastic, A4 - 305 x 220 mm				

LCS² ZONE DISTRIBUTION BOXES

Consolidation and redistribution made easy

Complete flexibility with the LCS² zone boxes:
centralisation of connections close to the workstation,
copper and fibre optics can be used together.



- Flexible installation with lines in reserve meet future requirements quickly.
- Guaranteed performance across the whole LCS² system.
- Fast, reliable connection to the LCS² zone box with sockets with copper and fibre optic feedthrough and RJ 45/RJ 45 cords.

N Available in cat. 6A

