

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [43031-0002](#)
Status: **Active**
Overview: Micro-Fit 3.0™ Connectors
Description: Micro-Fit 3.0™ Crimp Terminal, Male, with Gold (Au) Plated Tin/Brass Alloy Contact, 20-24 AWG, Reel

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-43045 \(PDF\)](#) [Product Literature \(PDF\)](#)
[Test Summary TS-43045-002 \(PDF\)](#)

General

Product Family	Crimp Terminals
Series	43031
Application	Power
Crimp Quality Equipment	Yes
Overview	Micro-Fit 3.0™ Connectors
Packaging Alternative	43031-0008 (Loose)
Product Literature Order No	987650-5984
Product Name	Micro-Fit 3.0™
UPC	800754369411


Physical

Gender	Male
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.061/g
Packaging Type	Reel
Plating min - Mating	0.381µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm²	N/A

Material Info

Reference - Drawing Numbers

Product Specification	PS-43045, RPS-43045-003, RPS-43045-004
Sales Drawing	SD-43031-****
Test Summary	TS-43045-002



EU RoHS

ELV and RoHS Compliant
REACH SVHC Contains SVHC: No
Low-Halogen Status Low-Halogen

China RoHS



Need more information on product environmental compliance?

Email productcompliance@molex.com
 For a multiple part number RoHS Certificate of Compliance, [click here](#)

Please visit the [Contact Us](#) section for any non-product compliance questions.

Search Parts in this Series

[43031Series](#)

Mates With

[43030 Micro-Fit 3.0™ Female Crimp Terminals](#)

Use With

[43020](#) , [43640 Micro-Fit 3.0™ Plug Housings](#), [44300 Micro-Fit BMI™ Panel Mount Plug Housings](#)

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Hand Crimp Tool	0638190000
FineAdjust™	0639004500
Applicator for Insulation OD	

1.30-1.85mm - 20-24 AWG T2 Terminator™ for insulation OD	<u>0639104500</u>
1.30-1.85mm - 20-24 AWG Insertion Tool for Crimp Terminal	<u>0638120800</u>
FineAdjust™ Applicator for Insulation OD	<u>0639018800</u>
1.10-1.30mm - 20-24 AWG FineAdjust™ Applicator for Insulation OD	<u>0639018900</u>
0.91-1.09mm - 20-24 AWG T2 Terminator™ for insulation OD	<u>0639118800</u>
1.10-1.30mm - 20-24 AWG T2 Terminator™ for insulation OD	<u>0639118900</u>
0.91-1.09mm - 20-24 AWG Extraction Tool	<u>0011030043</u>

This document was generated on 10/03/2014

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION