

02 06 180

High Leverage Combination Pliers



- 35 % less effort required than with conventional combination pliers
- easier work due to optimised leverage
- with cutting edges (hardness approx. 63 HRC) for soft and hard wire and piano wire
- long cutting edges for thicker cables
- with gripping zones for flat and round material, suitable for versatile use
- High-grade special tool steel, forged, oil-hardened



| | |
|---|--|
| Article No. | 02 06 180 |
| EAN | 4003773010012 |
| Pliers | chrome plated |
| Handles | insulated with multi-component grips, VDE-tested |
| Head | |
| Insulation standard | IEC 60900 DIN EN 60900 |
| hard wire Ø mm | 2,5 |
| piano wire Ø mm | 2,0 |
| Cutting capacity copper cable, multiple-stranded (diameter) Ø mm | 11,5 |
| Cutting capacity copper cable, multiple-stranded mm² | 16,0 |
| Length mm | 180 |
| Net weight g | 247 |

technical change and errors excepted

