



Specification

PD430 PD440 PD690 PD700
PD710 - Proving Units

Electrical

- PD430** Output voltage: First output level for 3s - 50V nominal
Second output level - 440V nominal
Output frequency: 50Hz nominal
- PD440** Output voltage: 440V nominal
Output frequency: 50Hz nominal
- PD690** Output voltage: 700V nominal
Output frequency: 50Hz nominal
- PD700** Output voltage: First output level for 3s - 50V nominal
Second output level - 700V nominal
Output frequency: 50Hz nominal
- PD710** Output voltage: 700V nominal
Output frequency: DC

All Units

Output loading: See typical output voltage vs. loading graph

Environmental

Operating temperature: -10°C to 40°C at max. 70% R.H.
Altitude: up to 2000m
Pollution degree: 2

General

Power: Internal batteries or external power source
Internal batteries: 6 x 1.5V, AA alkaline batteries (IEC LR6, NEDA 15A)
External power source: 12V DC max. at 2A min.
External power socket: 2.5mm jack socket, centre positive
Dimensions: 143 x 84 x 50mm.
Weight packed: 400g approx. with batteries
Includes: 6 x 1.5V AA alkaline batteries, instructions



Specification

PD430 PD440 PD690 PD700
PD710 - Proving Units

Typical Output Voltage vs. Loading

