



ACCENT



EUROline

**2270**  **BERNSTEIN** Accent

9-piece set dissipative tools with bright steel polished pliers.

**Weight:** 0.360 kg

No.	Description of individual tools
3-601-13	Side cutters, 120 mm, semi flush, for soft wire up to 1.5 mm and hard wire up to 0.4 mm Ø, bright steel-polished, box joint, double leaf spring, with dissipative black hand guard
3-633-13	Snipe nose pliers, 120 mm, plain jaws, bright steel-polished, box joint, double leaf spring, with dissipative black hand guard
4-601	Slotted screwdriver with dissipative handle, blade from chrome vandum, chrome-plated, with black tip, 50 x 0.8 mm
4-603	Slotted screwdriver with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip, 50 x 1.5 mm
4-621	Cross-recess screwdriver size 000, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
4-623	Cross-recess screwdriver size 0, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
5-191	Tweezers, made from conductive and acid-resistant black plastic material, reinforced with glassfibre, 120 mm, with straight, rounded tips
6-661	TORX-screwdriver T 5, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip
6-663 L	TORX-screwdriver T 7, with bore-hole in the tip, with dissipative handle, blade from chrome vanadium, chrome-plated, with black tip

**3-680**  **BERNSTEIN** EUROline-Conductive Set of pliers

4-piece set dissipative pliers from the series EUROline-Conductive to meet highest quality standards. **Weight:** 0.390 kg

No.	Description of individual tools
3-651-15	Mini side cutters EUROline-Conductive, 120 mm, flush, for soft wire up to 1.5 mm and medium hard wire up to 0.8 mm Ø, box joint, double leaf spring, fine polished and bright burnished, dissipative bicoloured hand guard
3-672-15	End cutters EUROline-Conductive, 130 mm, flush, for soft wire up to 0.8 mm Ø, cutting edge 20° angular, box joint, double leaf spring, fine polished and bright burnished, dissipative bicoloured hand guard
3-682-15	Flat nose pliers EUROline-Conductive, 130 mm, plain jaws, finish as before
3-683-15	Snipe nose pliers EUROline-Conductive, 130 mm, plain jaws, finish as before

3-970  **BERNSTEIN** TECHNICline Set of pliers

4-piece set dissipative pliers from the series TECHNICline in cases made from dissipative black imitation leather, with zip fastener

No.	Description of individual tools	Weight: 0.400 kg
3-963-15	Mini side cutters TECHNICline, 120 mm, ultra flush, for soft wire up to 1.3 mm Ø, medium hard wire up to 0.7 mm Ø, precision joint with screw system, double leaf spring, non-reflective surface, dissipative bicoloured hand guard	
3-971-15	Side cutters TECHNICline, 125 mm, semi flush, for soft wire up to 1.6 mm Ø, medium hard wire up to 1.0 mm Ø, hard wire up to 0.5 mm Ø, precision joint with screw system, double leaf spring, non-reflective surface, dissipative bicoloured hand guard	
3-992-15	Flat nose pliers TECHNICline, 130 mm, short plain jaws, finish as above	
3-683-15	Spitzzange TECHNICline, 140 mm, long plain jaws, finish as above	



3-970

## SIDE CUTTERS, TELEPHONE AND COMBINATION PLIERS

lap joint, bright polished – chrome–plated with dissipative black hand guard

No.	Length mm	Head- width mm	Finish	Cutting capacity		Weight g
				Wire soft	mm Ø hard	

### Side cutters

swedish design

3-133-13	145	19	special steel	2.5	1.25	155
----------	-----	----	---------------	-----	------	-----

### Telephone pliers

snipe nose, long straight jaws, with cutting edges for hard wire

3-245-13	200	18.5	serrated jaws			180
----------	-----	------	---------------	--	--	-----

### Combination pliers

with wire cutter, for hard wire

3-732-13	165	23	serrated jaws			185
----------	-----	----	---------------	--	--	-----



3-133-13



3-245-13



3-732-13

# SET OF ESD PLIERS



## 3-960 BERNSTEIN Set of ESD pliers

4-piece set black burnished pliers with dissipative hand guard, in a wallet of nylon



No.	Description of individual tools	Weight: 350 g
3-901-7	Side cutters, 120 mm, semi flush for soft wire up to 1.5 mm, for hard wire up to 0.4 mm Ø	
3-906-7	End cutters, 125 mm, with angular tips and oblique cutting edge, flush, for flush cutting, for soft wire up to 0.8 mm Ø	
3-932-7	Flat nose pliers, 120 mm	
3-933-7	Snipe nose pliers, 125 mm	

3-960

## 3-650 BERNSTEIN Set of conductive pliers

5-piece set bright steel-polished pliers with dissipative black handguard in a practical table support from conductive material

No.	Description of individual tools	Weight: 350 g
3-601-13	Side cutters, 120 mm, flush, for soft wire up to 1.5 mm, for hard wire up to 0.4 mm	
3-631-13	Round nose pliers, 120 mm, plain jaws	
3-632-13	Flat nose pliers, 120 mm, plain jaws	
3-633-13	Snipe nose pliers, 120 mm, plain jaws	
3-634-13	Snipe nose pliers, angular, 120 mm, plain jaws	



3-650