

64193NBU

NIGHT BREAKER UNLIMITED | Halogen headlight lamps for cars



Areas of application

- Headlight

Product benefits

- Up to 110 % more light on the road (compared to standard halogen lamps)
- Up to 40 m longer beam of light (compared to standard halogen lamps)
- Up to 20 % whiter light (compared to standard halogen lamps)
- Drivers spot obstacles and dangerous situations much sooner
- Optimum light for more reaction time
- Patented blue ring coating for less reflected glare
- More efficient light production thanks to optimized inert filling gas formula
- Higher resilience due to robust coil design

Product features

- Eye-catching design with partial blue coating and silver cap

Technical data

Electrical data

Power input	75 / 68 W ¹⁾
Nominal voltage	12 V
Test voltage	13.2 V

¹⁾ Maximum

Photometrical data

Color temperature	3900 K
Luminous flux	1650/1000 lm
Luminous flux tolerance	±15 %

Dimensions & weight

Length	82.0 mm
Diameter	13.0 mm
Product weight	21.30 g

Lifespan

Lifespan B3	80 / 260 h ¹⁾
Lifespan Tc	160 / 400 h ¹⁾

¹⁾ Filament 1 / Filament 2

Additional product data

Base (standard designation)	P43t
-----------------------------	------

Certificates & standards

ECE category	H4
--------------	----

Country specific categorizations

Order reference	64193NBU 60/55W
-----------------	-----------------

Country specific information

Product code	METEL-Code	SEG number	STK-Number	UK Org
4052899017214	-	8328014	-	-

Product datasheet

Logistical Data

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (height x width x length)	Volume	Gross weight
4052899017108	64193NBU	Hard Cover Box 2	95 mm x 47 mm x 115 mm	0.51 dm ³	126.60 g
4052899017115	64193NBU	Shipping carton box 20	106 mm x 240 mm x 250 mm	6.36 dm ³	1406.00 g
4052899017122	64193NBU	Folding carton box 1	71 mm x 47 mm x 47 mm	0.16 dm ³	29.30 g
4052899017139	64193NBU	Bundle 10	71 mm x 94 mm x 235 mm	1.57 dm ³	294.00 g
4052899017146	64193NBU	Shipping carton box 100	160 mm x 250 mm x 485 mm	19.40 dm ³	3062.00 g
4052899017153	64193NBU	Unpacked 1	- x - x -		
4052899017160	64193NBU	Shipping carton box 200	345 mm x 315 mm x 485 mm	52.71 dm ³	5702.00 g
4052899017177	64193NBU	Blister 1	51 mm x 95 mm x 135 mm	0.65 dm ³	32.30 g
4052899017184	64193NBU	Shipping carton box 10	146 mm x 115 mm x 335 mm	5.62 dm ³	415.00 g
4052899017191	64193NBU	Blister 2	51 mm x 140 mm x 135 mm	0.96 dm ³	59.60 g
4052899017207	64193NBU	Shipping carton box 20	146 mm x 146 mm x 475 mm	10.13 dm ³	754.00 g
4052899017214	64193NBU	Hard Cover Box 2	47 mm x 95 mm x 111 mm	0.50 dm ³	129.00 g
4052899017221	64193NBU	Shipping carton box 20	106 mm x 240 mm x 250 mm	6.36 dm ³	1392.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

Disclaimer

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.