


SSD64SSBS - Break Stem Open

General Part Information	
Product Description	SSD64SSBS
Article Number	78534.00
Rivet Type	i Break Stem Open
Standard Bulk Pack Quantity	4000.00
Application / Features	i 



Geometry / Dimensions / Performance	
Head Style	i Domed
Body Diameter Ø (mm)	4.80
Body Length (mm)	10.80
Min. Grip Range (mm)	3.20
Max. Grip Range (mm)	6.40
Min. Hole Diameter (mm)	4.90
Max. Hole Diameter (mm)	5.00
Min. Flange Diameter (mm)	9.06
Max. Flange Diameter (mm)	9.98
Flange Thickness (mm)	1.40
Mandrel Diameter (mm)	2.90
Nominal Shear Strength (N)	4400.00
Nominal Tensile Strength (N)	6100.00

Material / Finish / Weight	
Body Material	i Stainless Steel
Mandrel Material	Stainless Steel
Finish	Clean
Weight per thousand (kg)	3.58