

PSZROX-0415 - PSZROX

General Part Information

Product Description	PSZROX-0415
Article Number	33051
POPNut Type	i PSZROX
Standard Bulk Pack Quantity	10,000

Geometry / Dimensions

Thread Size	M4
Body Type (open / closed)	i Open
Body Features	i Round
Body Length (mm)	10.40
Min. Grip Thickness (mm)	0.50
Max. Grip Thickness (mm)	1.50
Head Style	i Reduced Head
Hole Diameter (mm)	6.40
Head Diameter (mm)	7.00
Head Thickness (mm)	0.60
Barrel Diameter (mm)	6.30

Material / Weight

Material	i Steel
Weight per thousand (kg)	1.2

