

# TouchNTuff® 93-250

CHEMICAL & LIQUID PROTECTION



STYLE #	COATING MATERIAL	CONSTRUCTION	GRIP DESIGN	CUFF STYLE	COLOUR	AQL	POWDER-FREE	EN SIZE	LENGTH MM	THICKNESS MM	PACKAGING
93-250	Nitrile	Unsupported	Ansell Grip Technology®	Beaded	Grey	1.5	Yes	5.5 - 6, 6.5 - 7, 7 - 7.5, 8 - 8.5, 8.5 - 9, 9.5 - 10	240	0.12	100 gloves per dispenser, 10 dispensers per shipper carton, 1000 gloves per shipper carton.

## DESCRIPTION

- Minimizes the force required to grip dry, wet or oily objects, reducing hand and arm fatigue and improving dexterity, safety and productivity.
- Proprietary nitrile formulation provides comfort for long wear periods.
- Offers high tensile strength and 3 times the puncture resistance of latex or PVC disposables.
- Resists a variety of industrial chemicals for longer periods than other nitrile disposable gloves
- Contains no natural rubber proteins, therefore protects against Type I skin allergies.
- No transfer of silicone contaminants to contact surface.

## FEATURED TECHNOLOGY

Ansell Grip



## Disposable Nitrile Glove with Ansell Grip Technology™

### PRIMARY INDUSTRIES



CATEGORY III



### IDEAL APPLICATIONS

- Compounding, mixing, blending
- Fastening, screwing & unscrewing parts
- Food handling
- Handling compression press and tablet manufacturing
- Handling of machined parts coated with light oil
- Handling of paint/glue guns & sprayers
- Inspection and tooling precision maintenance
- Lab work, blending, compounding, filling, cleaning
- Maintenance and equipment cleanup
- Picking and assembling wet or dry parts
- Using a V Blender to mix solids and colorants
- Wet chemical, particle and analytical testing

Print date: 28-10-2014

**Ansell Healthcare Europe N.V. (European Head Office)**

Riverside Business Park, Block J

Boulevard International 55, 1070 Brussels, Belgium

Tel. +32 (0) 2 528 74 00 • Fax +32 (0) 2 528 74 01 • Fax Customer Service +32 (0) 2 528 74 03

http://www.ansell.eu • E-mail info@ansell.eu

