

# Goggles

*uvex ultravision • ultrashield*

uvex ultravision • 9301

market favourite



9301-614

- exceptional wearer comfort
- ergonomically-designed with full vision
- sophisticated ventilation system
- soft face liners guarantee close and pressure-free fit
- fits over prescription spectacles
- quick and easy lens replacement
- available with custom bridge to fit smaller/narrower faces

*For more information on product please refer to the Goggle selection guide (page 41).*

uvex ultrashield • 9301

eye and face protection



9301-383F  
lower face guard



9301-382

- ultravision goggle fitted with lower face guard
- additional protection against coarse particles
- foam-padded breathing vents allow easy communication

*\* All products are AS/NZS 1337.1 medium impact approved*

*For more information on product please refer to the Goggle selection guide (page 41).*

# Goggles

## uvex ultrasonic • ultraguard

uvex ultrasonic • 9302

sleek sporty style



9302-345

- trendsetting design with full vision
- exceptional wearer comfort
- dual component technology (DCT) provides stability and pressure-free fit
- sophisticated ventilation system
- fits over most prescription spectacles (RX insert also available)
- quick and easy lens replacement



9302-049  
RX insert

For more information on product please refer to the Goggle selection guide (page 41).

uvex ultraguard • 9405

low profile comfort



9405-000

- low profile goggle
- indirect ventilation system
- soft face and nose padding provide exceptional wearer comfort
- frosted upper body to reduce reflection
- quick and easy lens replacement
- ideal for wearers of prescription eyewear
- compatible with half-face respirators

For more information on product please refer to the Goggle selection guide (page 41).

\* All products are AS/NZS 1337.1 medium impact approved

# Goggles

*uvex ultrasonic fire goggle • ultravision fire goggle*

uvex ultrasonic fire goggle • 9302 • ultravision fire goggle • 9301



Proud NSW RFS Technology Partner since 1991

- approved to NSW RFS specifications
- ventilation system design based on NSW RFS smoke hut test results
- resists smoke penetration whilst allowing humid air to escape
- heat resistant and flame retardant
- helmet and other PPE compatible
- optimised air volume to minimise eye damage from radiant heat
- anti-scratch and anti-fog approved to EN166



*type 2 fire goggle*

9301-342



*type 1 fire goggle*

9302-342

\* All products are AS/NZS 1337.1 medium impact approved

For more information on product please refer to the Goggle selection guide (page 41).

# Goggle selection guide

Part no.	Body	C/B	Vented					Foam liner		Lens material		Lens		Lower face guard		Replacement lens	
			yes	no	TVC	TVR	T&BVR	TVR & RX gap closed	open cell	closed cell	PC	Acetate	tint	coating	sold with		compatible
<b>ultravision</b>																	
9301-304	translucent		✓						✓		✓		clear	supravision		✓	9300-605F
9301-305	translucent		✓								✓		clear	supravision		✓	9300-605F
9301-323	translucent				✓					✓			clear	supravision		✓	9300-605F
9301-324	translucent				✓					✓			grey	supravision		✓	9300-607F
9301-342	red			✓					✓		✓		clear	supravision		✓	9300-605F
9301-363	translucent		✓						✓		✓		clear	THS		✓	9300-603F
9301-382	translucent		✓									✓	clear	anti-fog	✓	✓	9300-717F
9301-383	translucent		✓						✓			✓	clear	anti-fog	✓	✓	9300-717F
9301-383F	lower face guard only																
9301-384	translucent		✓								✓		clear	supravision	✓	✓	9300-605F
9301-385	translucent		✓						✓		✓		clear	supravision	✓	✓	9300-605F
9301-603	red			✓							✓		clear	supravision		✓	9300-605F
9301-614	translucent		✓									✓	clear	anti-fog		✓	9300-717F
9301-618	translucent		✓									✓	grey	anti-fog		✓	9300-219F
9301-620	translucent				✓						✓		clear	supravision		✓	9300-605F
9301-624	translucent		✓						✓			✓	clear	anti-fog		✓	9300-717F
9301-626	translucent				✓					✓		✓	clear	anti-fog		✓	9300-717F
9301-628	translucent		✓						✓			✓	grey	anti-fog		✓	9300-219F
9301-820	translucent				✓							✓	clear	anti-fog		✓	9300-717F
9301-905	translucent	✓	✓									✓	clear	anti-fog inside/ anti-scratch outside			n/a
<b>ultrasonic</b>																	
9302-049	RX insert only																
9302-342	red					✓					✓		clear	supravision			9302-615F
9302-345	orange/grey		✓								✓		clear	supravision			9302-615F
9302-346	orange/grey		✓								✓		grey	supravision			9302-616F
9302-347	orange/grey		✓								✓		SCT 400	supravision			9302-617F
9302-385	grey/black		✓								✓		clear	supravision			9302-615F
9302-386	grey/black		✓								✓		grey	supravision			9302-616F
9302-387	grey/black		✓								✓		SCT 400	supravision			9302-617F
9302-388	grey/black					✓					✓		clear	supravision			9302-615F
9302-389	grey/black					✓					✓		grey	supravision			9302-616F
9302-390	grey/black				✓						✓		clear	THS			9302-620F
9302-391	grey/black				✓						✓		SCT 400	THS			n/a
9302-395	grey/black						✓				✓		clear	supravision			9302-615F
9302-396	grey/black						✓				✓		grey	supravision			9302-616F
<b>ultraguard</b>																	
9405-000	translucent		✓									✓	clear	anti-fog inside/ anti-scratch outside			n/a
<b>classic</b>																	
9305-516	translucent		✓									✓	clear	anti-fog			9305-517F

**Legend:** C/B - custom bridge to fit smaller/narrower faces    TVC - top vent closed    TVR - top vent reduced  
T&BVR - top & bottom vents reduced    PC - polycarbonate    TVR & RX gap closed - top vent reduced & not compatible with RX insert