



## Vyna-Plush

### The perfect low cost doormat

- Budget doormat offering all-round performance.
- Scrapes dirt and wipes moisture.
- 100% Polypropylene fibre 'scraping' surface.
- Slip and stain-resistant PVC 'stay in place' backing.

Overall product height: 7mm (pile height: 4mm)

Total weight: 2.6kg/m<sup>2</sup>



Red



Brown



Blue



Steel

| Dimensions (m.)        | Weight Kg | Packaging Dimensions (cm.) | Packaging Type | Packaging Volume (m.) | Packaging Quantity | Colour      | Part Code |
|------------------------|-----------|----------------------------|----------------|-----------------------|--------------------|-------------|-----------|
| 0.6 x 0.9              | 2         | 17.5 x 17.5 x 75           | Box            | 0.02                  | 1                  | Black/Steel | VP010601  |
|                        |           |                            |                |                       |                    | Black/Red   | VP010301  |
|                        |           |                            |                |                       |                    | Black/Blue  | VP010201  |
|                        |           |                            |                |                       |                    | Black/Brown | VP010501  |
| 0.9 x 1.2              | 2         | 17.5 x 17.5 x 105          | Box            | 0.02                  | 1                  | Black/Steel | VP010602  |
|                        |           |                            |                |                       |                    | Black/Red   | VP010302  |
|                        |           |                            |                |                       |                    | Black/Blue  | VP010202  |
|                        |           |                            |                |                       |                    | Black/Brown | VP010502  |
| 0.9 x 1.5              | 2         | 17.5 x 17.5 x 105          | Box            | 0.02                  | 1                  | Black/Steel | VP010603  |
|                        |           |                            |                |                       |                    | Black/Red   | VP010303  |
|                        |           |                            |                |                       |                    | Black/Blue  | VP010203  |
|                        |           |                            |                |                       |                    | Black/Brown | VP010503  |
| 1.2 x 1.8              | 2         | 23 x 23 x 124              | Box            | 0.02                  | 1                  | Black/Steel | VP010604  |
|                        |           |                            |                |                       |                    | Black/Red   | VP010304  |
|                        |           |                            |                |                       |                    | Black/Blue  | VP010204  |
|                        |           |                            |                |                       |                    | Black/Brown | VP010504  |
| 0.9 x per linear metre |           |                            | Box            |                       | 1                  | Black/Steel | VP010608C |
|                        |           |                            |                |                       |                    | Black/Red   | VP010307C |
|                        |           |                            |                |                       |                    | Black/Blue  | VP010207C |
|                        |           |                            |                |                       |                    | Black/Brown | VP010507C |
| 1.2 x per linear metre |           |                            | Box            |                       | 1                  | Black/Steel | VP010608C |
|                        |           |                            |                |                       |                    | Black/Red   | VP010308C |
|                        |           |                            |                |                       |                    | Black/Blue  | VP010208C |
|                        |           |                            |                |                       |                    | Black/Brown | VP010508C |

Continued on next page

### United Kingdom

COBA Europe Ltd  
Marlborough Drive  
Fleckney, Leicestershire  
LE8 8UR

+44 (0)116 240 1088  
sales@cobaeeurope.com  
www.cobaeeurope.com

### Germany

COBA Europe GmbH  
Pullenweg 1 - 3  
41352 Korschenbroich

+49 (2161) 2945-0  
verkauf@cobaeeurope.de  
www.cobaeeurope.de

### Slovakia

COBA Europe s.r.o.  
Terchová - Vyšné Kamenec 11  
SK-013 06

+421 41 507 11 12  
sales@cobaeeurope.sk  
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.

## Technical Features:

## According to:

|                       |                              |   |
|-----------------------|------------------------------|---|
| Manufacturing Process | ISO 2424 / BS 5557           | Vuilvang  |
| Surface Aspect        |                              | Cutpile   |
| Pile material         |                              | 100% PA   |
| Primary Backing       | ISO 2424 / BS 5557           | Collback TM80   |
| Machine gauge         | DIN 61151 / BS 5557          | 5/32" COC   |
| Backing               | ISO 2424                     | PVC US  |
| Pile Height           | ISO 1766 / BS 4223 Clause 10 | 4.0 mm .16 in   |
| Total Height          | ISO 1765 / BS 4051           | 7.0 mm .28 in   |
| Pile Weight           | 400 g/m <sup>2</sup>         | 11.8 oz/yd <sup>2</sup> (+/-7,5%)                       |
| Total Weight          | ISO 8543 / BS 4223 Clause 7  | 2660 g/m <sup>2</sup> 78.4 oz/yd <sup>2</sup> (+/-7,5%) |
| Number of tufts       | ISO 1763 / BS 4223 Clause 6  | 65500 1/m <sup>2</sup> 55000 1/yd <sup>2</sup>          |

## Performances:

|                                   |                               |                           |
|-----------------------------------|-------------------------------|---------------------------|
| Walking test                      | EN 1815 / ISO TR 6356 / DD68  | < 2 KV                    |
| Dimensional Stability             | EN 986 / ISO 2551 / DIN 54318 | Voldoet aan de norm(pass) |
| Electrical resistivity            | IBM/ ICL                      | -                         |
| Electrical resistivity vertical   | DIN 54345                     | -                         |
| Electrical resistivity horizontal | DIN 54345                     | -                         |
| Sound Insulation                  | ISO 140-8 / BS 3638           | >= 19dB                   |
| Thermal retention                 | ISO 8302 / DIN 52612          | -                         |
| Soiling (dry / wet)               | EN 1289                       | 4.5                       |

## Colour fastness:

|                |                                  |   |
|----------------|----------------------------------|---|
| To light       | ISO 105 B02 / DIN 54004/ BS 1006 | 5 |
| To water       | ISO 105 E01 / DIN 54006/ BS 1006 | 5 |
| To seawater    | ISO 105 E02 / DIN 54007/ BS1006  | - |
| To shampoo     | BS 1006                          | 5 |
| To rubbing dry | ISO 105 X12/ DIN 54021/BS1006    | 4 |
| Wet            |                                  | 4 |

## Flammability rating:

|                             |                                |            |
|-----------------------------|--------------------------------|------------|
| NBS Flooring Radiant        | ASTM E648/DIN 4102/NEN 1775    | -          |
| Pill (Tablet) test          | ISO 6925 = ASTM D2829/ BS 6307 | -          |
| Hot Metal Nut               | BS 4790/BS 5287                | Low radius |
| UK Radiant panel test       | BS 476 (7)                     | -          |
| Austrian radiant panel test | Oenorm 3810 / Oenorm 3800 (1)  | -          |
| Kleinfrenner                | DIN 54332 / NEN 1775 (1)       | Ta (B2)/T3 |
| Panneau radiant             | NF P-92-506                    | -          |

Gut certificate no. 20249

European Overall Classification EN 1307 2LC1

Strapazierwert DIN 66095 (2)

Komfortwert DIN 66095 (2)

Continued on next page

### United Kingdom

COBA Europe Ltd  
Marlborough Drive  
Fleckney, Leicestershire  
LE8 8UR

+44 (0)116 240 1088  
sales@cobaeeurope.com  
www.cobaeeurope.com

### Germany

COBA Europe GmbH  
Pullenweg 1 - 3  
41352 Korschenbroich

+49 (2161) 2945-0  
verkauf@cobaeeurope.de  
www.cobaeeurope.de

### Slovakia

COBA Europe s.r.o.  
Terchová - Vyšné Kamenec 11  
SK-013 06

+421 41 507 11 12  
sales@cobaeeurope.sk  
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.

**Adhesive Recommendations:**

| Trade Mark | Backing | Type of bond |         |                        |
|------------|---------|--------------|---------|------------------------|
|            |         | Permanent    | Release | Heavy Duty / Wet Areas |
| Vynaplush  | PVC     | ----         | F41     | F74, F81, F84          |

Please contact us for more information on Styccobond adhesives.

**End of Document**

**United Kingdom**

COBA Europe Ltd  
Marlborough Drive  
Fleckney, Leicestershire  
LE8 8UR

+44 (0)116 240 1088  
sales@cobaeeurope.com  
www.cobaeeurope.com

**Germany**

COBA Europe GmbH  
Pullenweg 1 - 3  
41352 Korschenbroich

+49 (2161) 2945-0  
verkauf@cobaeeurope.de  
www.cobaeeurope.de

**Slovakia**

COBA Europe s.r.o.  
Terchová - Vyšné Kamenec 11  
SK-013 06

+421 41 507 11 12  
sales@cobaeeurope.sk  
www.cobaeeurope.sk

The information contained within this datasheet is for guidance only. The data and suggested application are not exhaustive. All dimensions quoted are nominal figures. Please note that some products may be subject to a degree of shrinkage when installed into some applications.