



-1. Torque tools

-1.1. TORQUE TOOLS

- Dial torque wrench
- Accuracy $\pm 4\%$
- Visual signal
- Reversible operation
- Dual scale in metric and imperial
- Memory needle
- Anti-shock protected dial
- With rubber sleeve in 1/4", 3/8" and 1/2" models

Dial torque wrenches, double scale

7454

7454-3	7314150119493	1	1/4	0-3.5	0-2.6	0-30	0.1	292	499
7454-9	7314150119509	1	1/4	0-9	0-6.6	0-75	0.2	292	499
7454-18	7314150119516	1	3/8	0-18	0-13.3	0-150	0.5	292	499
7454-35	7314150119523	1	3/8	0-35	0-25.8	0-300	1	292	499
7454-70	7314150119530	1	3/8	0-70	0-50	0-620	2	381	726
7454-140	7314150119547	1	1/2	0-140	0-100	0-1239	5	552	1680
7454-240	7314150119554	1	1/2	0-240	0-175	0-2124	5	552	1680
7454-350	7314150119561	1	1/2	0-350	0-250	0-3098	10	552	1680
7454-480	7314150119578	1	3/4	0-480	0-350	0-4248	10	711	2611
7454-800	7314150119585	1	3/4	0-800	0-600	0-7081	20	1194	4585
7454-1400	7314150119592	1	1"	0-1400	0-1000	0-12391	25	1880	13620
7454-800E	7314150119608	1	3/4	0-800	0-600	0-7081	20	1194	4585
7454-1400E	7314150119615	1	1"	0-1400	0-1000	0-12391	25	1880	13620

