



- Rework station
- Power unit, 3 channels with soldering iron WP 80, desoldering iron DSX 80 and hot air iron HAP 200
- Large allround set for all repair jobs
- Desoldering iron DSX 80 for horizontal applications

WR 3000M Set

Code No.: T0053368699

Dimensions W x D x H (mm)	280 x 240 x 103 mm
Dimensions W x D x H (Inch)	11,02 x 9,45 x 4,06 Inch
Weight (ca) in kg	7,3 kg
Voltage	230 V
Power output	400 W
Channels	3
Temperature range (depends on tool) °C	50 - 550
Temperature range (depends on tool) °F	150 - 950
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding	Via 3.5 mm pawl socket on back of device (Hard grounded)
Display	LCD
Air consumption l/min	---
Operating pressure	---
Capacity l/min	18
Vacuum	0,7 bar