



|                           |                       |
|---------------------------|-----------------------|
| <b>Model:</b>             | <b>CS 50</b>          |
| <b>Pression max.:</b>     | <b>8 bars</b>         |
| <b>Capacity:</b>          | <b>24 liters</b>      |
| <b>Production:</b>        | <b>50 liters/min</b>  |
| <b>Sound level:</b>       | <b>43 dB (A)</b>      |
| <b>Power:</b>             | <b>Yes</b>            |
| <b>Net weight:</b>        | <b>30 kg</b>          |
| <b>Electrical Supply:</b> | <b>230 V. 50/60Hz</b> |

This compressor is perfect in areas where loud noises are not allowed: laboratory, education, research center etc.

- Very silent model
- Easy to handle
- Compact
- Strong
- Equipped in serial with a pressure-reducer c/w 40 microns filter

The compressor is delivered with quick coupling kit, 3 meters of plastic flex and 40 microns air filter.

