














ROOF

COVERS SCREWS

	ORDER SYMBOL	FOR COVERS
 Wing head screw	HS 10255	30
 Slotted head screw, sealable	SS 10535	30
 Triangle head screw	DS 10581	30/80/100
 Cross head screw	CS 10256	30/100
 Slotted head screw, quick-lock, *)	SS 10544	30/100
 Wing head screw, quick-lock, *)	HS 10533	30
 Quick-locking wing head screw, hinged, *)	HS 10532	30
 *) Threaded bushing	MB 10534	
 *) Threaded bushing (needed for quick-locking screws)		
 Cross head screw	SS 10563	80
 Wing head screw	HS 10562	80
 Noryl slotted head screw (good chemical resistance)	SS 10256N	30
 Noryl wing head screw (good chemical resistance)	HS 10255N	30
Set of four cross head screws	SS 10256-4	30/100
Set of six cross head screws	SS 10256-6	30/100
Set of four cross head screws	SS 10563-4	80

SOLID FRAME

	ORDER SYMBOL	SIZE mm
 Frame, with opening	Cover 28/28-0	280x280
 Front plate aluminium	FP 28/28	
Frame, no opening	Cover 28/28-D	280x280
Key lock set	MR 26065	














Solid Frames also fit EKOE and SOLID 2805 tests.

KEY-LOCK SET

	ORDER SYMBOL
 Key-lock set incl., lock and 2 keys for 30 mm covers	MB 10597

INSPECTION WINDOWS

The order symbol indicates the amount of the DIN module for example L08=8 modules.

	ORDER SYMBOL	SIZE mm
 Windows, IP 65	L12 II	248x128
 Windows, IP 65	L24 II	248x128
 Windows, IP 65	L12	248x128
 Windows, IP 65	L24	248x128
 Windows, IP 65	L13	257x108
 Windows, IP 54	L10	199x77
 Windows, IP 54	L08	162x77
 Windows, IP 54	L06	130x77
 Windows, IP 54	L04	96x77
 Windows, IP 54	L02	60x77
 Front plates for L 12 windows	B12 10621-4S	
 Front plates for L 24 windows	B24 10620-4S	
 Large size windows, IP 65, for enclosure EKW 100-G	L44 II	377x331
	L43 II	331x277



L 12 clear



L 12 II transparent smoked grey



L 13 clear



SOLID FRAME application



L 24 clear



L 44 II transparent smoked grey



L 43 II transparent smoked grey