



RoHS

IP67

REV.	DESCRIPTION	DATE
A	ISSUE	Dec/23/2013
B	Modify the wire diagram.	Dec/25/2013
C	Modify M12 Pin Assignment.	Dec/25/2013
D	Modify cable length.	Dec/25/2013
D1	Correct key direction.	Jan/22/2014
E	Add note.	Mar/30/2014
F	Modify P/N.	Sep/25/2014
G	Modify connector to shielding type.	Nov/12/2014
G1	Change ring nut to shielding type.	Nov/25/2014



No.	PART NAME	DESCRIPTION	COLOR	Q'TY	REMARKS
7	SHIELD	Brass, Nickel Plated.		1	
6	RJ45 PLUG	RJ45 8P8C PLUG (shielding type).		1	
5	CABLE	CAT5E FTP 24AWG x 4 PAIR + AL/MY + Drain wire.	BLACK	1	WAC2B0026
4	RING NUT	Brass, Nickel Plated.		1	M12S-RN-D985
3	O-RING	Viton.	BLACK	1	M12-O-VK
2	CONTACT	Brass , Female pin ,6 u" Gold plated .		8	AASPF-1008-0.8
1	CONNECTOR	M12 X-coding Female connector insert. Nylon+GF.	BLACK	1	M12X-08F

Customer: FLIR				
 	UNIT: mm	TITLE	M12 X-Coding Female Molded Cable Ass'y	
	SCALE			
UNLESS OTHERWISE SPECIFIED TOLERANCES:		P/N:	K129351004	DR. Stanley
X ± 0.25	XX ± 0.1			CH. ERIC
XXX ± 0.05	ANGLE ± 1°X	REV.	DWG.NO:	AP.
G1	1/1		T128390	