














# Polycom Conference Phone Guide

| IP conference phones                           | Large room  | Standard conference room  |  | Small room and office   |   |
|--|---|---|--|---|---|
|  | Polycom® SoundStation® IP 7000<br> | Polycom® SoundStation® Duo<br> | Polycom® CX3000<br> | Polycom® SoundStation® IP 6000<br> | Polycom® SoundStation® IP 5000<br> |
| <b>Network connectivity</b>                    |   |   |  |   |   |
| Analog   |   | •   |  |   |   |
| IP (SIP)                                       | •   | •   |  | •   | •   |
| Microsoft® Lync®                               |   | •   | optimized  |   | •   |
| Digital PBX                                    |   |   |  |   |   |
| <b>Voice quality</b>                           |   |   |  |   |   |
| Polycom® HD Voice™ technology                  | •   | •   | •  | •   | •   |
| Loudspeaker frequency response                 | 160 Hz—22 kHz   | 220 Hz—7 kHz  | 200 Hz—7 kHz   | 220 Hz—14 kHz   | 250 Hz—7 kHz  |
| Microphone pickup range                        | 6 m/20 ft   | 3 m/10 ft   | 3.6 m/12 ft  | 3.6 m/12 ft   | 2 m/7 ft  |
| Intelligent microphone mixing                  | •   | •   | •  | •   | •   |
| Dynamic noise reduction                        | •   | •   | •  | •   | •   |
| Automatic gain control                         | •   |   | •  | •   |   |
| <b>Additional features</b>                     |   |   |  |   |   |
| Resists interference from wireless devices     | •   | •   | •  | •   |   |
| Software upgradable                            | •   | •   | •  | •   |   |
| Large display to support advanced applications | •   |   | •  |   |   |
| Multi-unit connectivity                        | •   |   |  |   |   |
| Connect to external audio system               | • <sup>(1)</sup>  |   |  |   |   |
| Computer/mobile device connectivity            | •   |   |  |   | •   |
| <b>Optional accessories</b>                    |   |   |  |   |   |
| Expansion microphones (wired)                  | •   | •   | •  | •   |   |
| Wireless lapel pin microphone                  | • (NA only)   |   |  | • (NA only)   |   |
| Video integration kit or cables                | •   |   |  |   |   |
| Computer calling kit                           |   | •   |  |   |   |
| Mobile device cables                           | •   | •   |  |   |   |
| <b>Model variants</b>                          |   |   |  |   |   |
| Power over Ethernet (PoE)                      | 2200-40000-001  |   | 2200-15810-025   | 2200-15600-xxx  | 2200-30900-025  |
| AC or Power over Ethernet (PoE)                | 2230-40300-001  | 2200-19000-xxx  |  | 2200-15660-xxx  | 2200-30900-xxx  |
| AC Power only                                  |   |   |  |   |   |

<sup>1</sup> Optional accessory required

| Analog conference phones                       | Large room   | Standard conference room   |  |   | Small room and office   |   |
|--|--|--|--|---|---|---|
|  | Polycom® SoundStation VTX 1000®<br> | Polycom® SoundStation2™<br> | Polycom SoundStation Duo<br> | Polycom® SoundStation2W™<br> | Polycom® VoiceStation® 500<br> | Polycom® VoiceStation® 300<br> |
| <b>Network connectivity</b>                    |  |  |  |   |   |   |
| Analog   | •  | •  | •  | •   | •   | •   |
| IP (SIP)                                       |  |  | •  |   |   |   |
| Microsoft Lync                                 |  |  | •  |   |   |   |
| Digital PBX                                    |  | • <sup>(1)</sup>   |  |   |   |   |
| <b>Voice quality</b>                           |  |  |  |   |   |   |
| Polycom HD Voice technology                    |  |  | •  |   |   |   |
| Loudspeaker frequency response                 | 80 Hz–7 kHz <sup>(3)</sup>   | 300 Hz–3300 Hz   | 220 Hz–7 kHz   | 300 Hz–3500 Hz  | 300 Hz–3300 Hz  | 300 Hz – 3300 Hz  |
| Microphone pickup range                        | 6 m/20 ft  | 3 m/10 ft  | 3 m/10 ft  | 3 m/10 ft   | 2 m/7 ft  | 2 m/7 ft  |
| Intelligent microphone mixing                  | •  | •  | •  | •   | •   | •   |
| Dynamic noise reduction                        | •  | •  | •  | •   | •   | •   |
| Automatic gain control                         | •  |  |  |   |   |   |
| <b>Additional features</b>                     |  |  |  |   |   |   |
| Resists interference from wireless devices     | •  | •  | •  | •   | •   | •   |
| Software upgradable                            | •  |  | •  | •   |   |   |
| Large display to support advanced applications |  |  |  |   |   |   |
| Multi-unit connectivity                        |  |  |  |   |   |   |
| Connect to external audio system               | •  | •  |  | •   |   |   |
| Bluetooth connectivity                         |  |  |  |   | •   |   |
| <b>Optional accessories</b>                    |  |  |  |   |   |   |
| Expansion microphones (wired)                  | •  | • <sup>(2)</sup>   | •  | • <sup>(2)</sup>  |   |   |
| Wireless lapel pin microphone                  | •  | •  |  |   |   |   |
| Video integration kit or cables                | •  |  |  |   |   |   |
| Computer calling kit                           |  | • <sup>(2)</sup>   | •  | • <sup>(2)</sup>  | •   |   |
| Mobile device cables                           |  | • <sup>(2)</sup>   | •  | • <sup>(2)</sup>  | •   |   |
| <b>Model variants</b>                          |  |  |  |   |   |   |
|  | 2200-07142-xxx (with EX mics only)   | 2200-15100-xxx (non expandable w/o display)  | 2200-19000-xxx   | 2200-07800-xxx (expandable)   | 2200-17900-xxx  | 2200-17910-xxx  |
|  | 2200-07300-xxx (w/o EX mics and subwoofer)   | 2200-16000-xxx (non-expandable, w/display)   |  | 2200-07880-xxx (basic)  |   |   |
|  | 2200-07500-xxx (with subwoofers only)  | 2200-16200-xxx (expandable, w/display)   |  |   |   |   |

<sup>1</sup> Models available with integration to selected digital PBX. See product details for more information.

<sup>2</sup> Available on selected models

<sup>3</sup> SoundStation VTX to SoundStation VTX