



## DATA SHEET

---

# Polycom® SoundStation® IP Conference Phones

The family of Polycom® SoundStation® IP conference phones delivers unbeatable clarity and performance for any size room—from executive offices to board rooms. Don't settle for a desk phone in your conference room—only Polycom IP conference phones deliver the superior audio performance and 360° microphone pickup required for efficient and productive conference calls while leveraging your existing VoIP infrastructure for maximum cost savings.

**Polycom® SoundStation® IP 7000**—Astounding voice quality and clarity from the world's most advanced IP conference phone



- 22 kHz CD-quality Polycom® HD Voice™ technology for life-like clarity and Intelligibility
- 20-foot (6.1 m) microphone pickup range, more with optional expansion mics
- Resists interference from mobile phones and other wireless devices
- Connect two units together for additional microphone pickup and speaker volume
- Large high resolution display and processing power for IP applications
- Integration with Polycom HDX® and Polycom® RealPresence® Group Series® high definition video conferencing systems
- Integrated Power over Ethernet (PoE) connectivity
- Applications Port for mobile device and computer connectivity

**Polycom® SoundStation® IP 6000**—Sophisticated IP conference phone designed for midsize rooms



- 14 kHz Polycom HD Voice for remarkable clarity and intelligibility
- 12-foot (3.6 m) pickup range, more with optional expansion mics
- Resists interference from mobile phones and other wireless devices
- High resolution backlit display for vital call information and multi-language support
- Integrated Power over Ethernet (PoE) connectivity

**Polycom® SoundStation® Duo**—Highly reliable dual-mode conference phone for small to midsize conference rooms



- IP and circuit-switched telephony platform support
- 7 kHz Polycom HD Voice for remarkable clarity and intelligibility
- 10-foot (3 m) microphone pickup range, more with optional expansion mics
- Resists interference from mobile phones and other wireless devices
- High resolution backlit display for vital call information and multi-language support
- Integrated Power over Ethernet (PoE) connectivity
- Applications Port for mobile device and computer connectivity
- Corporate Directory (LDAP) integration
- Failover/failback from IP to circuit-switched

**Polycom® SoundStation® IP 5000**—Advanced IP conference phone designed for small conference rooms and executive offices



- 7 kHz Polycom HD Voice for remarkable clarity and intelligibility
- 7-foot (2.1 m) microphone pickup range
- Resists interference from mobile phones and other wireless devices
- High resolution backlit display for vital call information and multi-language support
- Integrated Power over Ethernet (PoE) connectivity
- Small footprint for executive offices and small conference tables

	Polycom SoundStation IP 5000	Polycom SoundStation Duo	Polycom SoundStation IP 6000	Polycom SoundStation IP 7000
Polycom HD Voice Technology	Up to 7 kHz	Up to 7 kHz	Up to 14 kHz	Up to 22 kHz
Mic pickup range	7 feet/2.1 m	10 feet/3 m	12 feet/3.6 m	20 feet/6.1 m
Optional EX mics available		•	•	•
Speaker loudness	Smaller room	Small to midsize room	Midsize room	Larger room
Dynamic noise reduction	•	•	•	•
Intelligent mic mixing	•	•	•	•
Display	High resolution	High resolution	High resolution	Large multi-line high resolution
Local application support	Limited	Limited	Limited	Full
Integrated Power over Ethernet (PoE)	•	•	•	•
Reduced mobile phone interference	•	•	•	•
Mobile device/ computer connections		•		•
Multi-unit connectivity				•
External speaker support				•
RealPresence Group Series and HDX video integration				•
Failover/failback to analog		•		

Need flexible financing?

Polycom **CAPITAL**  
Collaborative Financing

[www.polycom.com/polycom-capital](http://www.polycom.com/polycom-capital)

### About Polycom

Polycom is the global leader in open standards-based unified communications and collaboration (UC&C) solutions for voice and video collaboration, trusted by more than 415,000 customers around the world. Polycom solutions are powered by the Polycom® RealPresence® Platform, comprehensive software infrastructure and rich APIs that interoperate with the broadest set of communication, business, mobile and cloud applications and devices to deliver secure face-to-face video collaboration in any environment.

Polycom, Inc.  
1.800.POLYCOM  
[www.polycom.com](http://www.polycom.com)

Polycom Asia Pacific Pte Ltd  
+65 6389 9200  
[www.polycom.asia](http://www.polycom.asia)

Polycom EMEA  
+44 (0)1753 723282  
[www.polycom.co.uk](http://www.polycom.co.uk)

