



ENGLISH

Datasheet  
**LED 3AA 500LM High Power Focusing  
Torch**

RS Stock No: 901-4976





ENGLISH

### Sizes:

Torch Overall Length (mm): 141

Diameter (Ø mm): Head - Ø 41.5, Barrel – Ø 37.5

Batteries Inserted: 3 X AA

Batteries Supply: Included

Weight (gm), Torch Only: 171.4

### Materials/Parts:

Case: 6463 Aluminium Alloy

Lens: PC

LED: CREE X-PL V4

Package: Folded PVC Blister with RS Card Inserted

### Features:

Depressing Tail Cap Switch

**Switching Modes – High ON/Low ON/Flash ON/OFF**

Functioned by 3 X AA Batteries

Carrying Holster Included

**Slide Focus from Flood to Spot**

**Built-in Multi Option Battery Holder in Use – 3 X AA, 2 X AA or 1 X AA**

Lumen Output (**ANSI FL1 STANDARD**):

**3 X AA – 500 LM at High, 150 LM at Low**

**2 X AA – 280 LM at High, 95 LM at Low**

**1 X AA – 120 LM at High, 40 LM at Low**

Battery Run Time (100% to 10%, **ANSI FL1 STANDARD**):

**3 X AA – 9 Hrs at High, 27 Hrs at Low**

**2 X AA – 6.5 Hrs at High, 19.5 Hrs at Low**

**1 X AA – 4.5 Hrs at High, 13.5 Hrs at Low**



**ENGLISH**

**Battery Power Indicator:** On Grip, the indicator turned from GREEN to RED when power is less than 20%

**Water Resistant:** IPX6

**Drop Impact Test:** 1 Meter

**Taiwan and USA Patented**

**Colour:**

Metal Pewter Anodized Colour

**Marking:**

RS Laser Engraved Logo on Torch