



ENGLISH

Datasheet

# LED 3AA 400LM High Power Magnetic Work Light

RS Stock No: 901-4988





ENGLISH

### **Sizes:**

Torch Overall Length (mm): 580 (Including Flexible Shaft)

Diameter (Ø mm): Head - Ø 18, Barrel – Ø 39

Batteries Inserted: 3 X AA

Batteries Supply: Included

Weight (gm), Torch Only: 260

### **Materials/Parts:**

Case: 6463 Aluminium Alloy

Lens: PC

LED: CREE X-PE TORCH

Package: Folded PVC Blister with RS Card Inserted

### **Features:**

Depressing Barrel Switch

**Switching Modes – High ON/Low ON/OFF**

Functioned by 3 X AA Batteries

Carrying Holster Included

**Built-in Multi Option Battery Holder in Use – 3 X AA, 2 X AA or 1 X AA**

Lumen Output (**ANSI FL1 STANDARD**):

**3 X AA – 400 LM at High, 150 LM at Low**

**2 X AA – 150 LM at High, 50 LM at Low**

**1 X AA – 100 LM at High, 30 LM at Low**

Battery Run Time (100% to 10%, **ANSI FL1 STANDARD**):

**3 X AA – 9 Hrs at High, 27 Hrs at Low**

**2 X AA – 6.5 Hrs at High, 19.5 Hrs at Low**

**1 X AA – 4.5 Hrs at High, 13.5 Hrs at Low**



ENGLISH

**Magnet:** One Strong Magnet on the base and the other small magnet stored in the tail cap to be Installed on the front as necessary in use.

**Battery Power Indicator:** On Grip, the indicator turned from GREEN to RED when power is less than 20%

Water Resistant: IPX6

Drop Impact Test: 1 Meter

Taiwan and USA Patented

**Colour:**

Metal Pewter Anodized Colour

**Marking:**

RS Laser Engraved Logo on Torch