



ENGLISH

Releasable Metal Cable Ties



Product Specification

Releasable Tie offers greater flexibility through it's Fasten-unfasten-refasten capability.

Normal operating range for the uncoated ties is -40°C to $+300^{\circ}\text{C}$ and for the Coated version is -60°C to $+165^{\circ}\text{C}$. Coated ties have better weathering properties with excellent resistance to corrosion, radiation and abrasion.

Material: Stainless Steel (316 grade),

Approval: DNV, Lloyd's, UL, ABS

Application: Marine, chemical, oil & gas, Maintenance



ENGLISH

Dimensions

RS Article	Colour	Length (mm)	Width (mm)	Quantity	Max Bundle Dia. (mm)
185-8670	Black	230	5	100	60
547-4399	Black	230	10	100	60
185-8686	Black	330	5	100	95
185-9364	Black	330	10	100	95
547-4406	Black	450	10	100	130