




ENGLISH

## Non-Releasable Stainless Steel Cable Tie



### Product Specification

Roller ball cable tie design which is self locking and fast & easy to install. It can be tightened by hand or with a tool.

The normal operating range for the roller ball uncoated ties version is  $-80^{\circ}\text{C}$  to  $+538^{\circ}\text{C}$  approximately.

For the coated version, the normal operating range is  $-80^{\circ}\text{C}$  to  $+150^{\circ}\text{C}$ . Coating is non toxic halogen free Polyester. It is available in wide choice of colours.

**Material:** Stainless Steel (316 grade), available with black polyester/epoxy resin coating

**Approval:** DNV, Lloyd's, UL, ABS

**Application:** Marine, chemical, oil & gas, Maintenance



ENGLISH

## Datasheet

### Non-Releasable Stainless Steel Cable Tie

RS Part No.	Length mm	Width mm	Max Bundle Dia
1595329	360	4.6	100
1595313	200	7.9	50
1595357	150	4.6	50
1595335	360	7.9	100
5474305	520	4.6	150
5474311	520	7.9	150
7436162	680	4.6	200
7436166	380	7.9	200
7436172	1000	4.6	300
7436178	840	7.9	250
7436181	1000	7.9	300

### Coated Stainless Steel Cable Tie

RS Part No	Length mm	Width mm	Max Bundle Dia
5474327	150	4.6	50
5474333	360	4.6	100
5474349	250	4.6	150
5474355	200	7.9	50
5474377	360	7.9	100
5474383	520	7.9	150