

Product Datasheet

Stainless Steel Cable Ties



Product Specification

Material: Stainless Steel (316 grade), available with black polyester/epoxy resin coating

Temperature: Uncoated : - 80°C ~ + 539°C Coated : - 80°C ~ + 150°C

Type: Non-releasable, ladder cable ties

Approval: Lloyd's, UL, ABS

Application: Marine, chemical, oil & gas, Maintenance

Dimensions:

RS Article	Material	Colour	Width (mm)	Length (mm)	Min. Tensile Strength (Kg.)	Max Bundle Dia. (mm)
121-618	SS 316	Silver	7	225	46	70
121-624	SS 316	Silver	7	300	46	95
121-630	SS 316	Silver	7	610	46	190
121-646	SS 316	Silver	12	610	114	190
121-652	SS 316 (coated)	Black	7	225	46	70
121-668	SS 316 (coated)	Black	7	300	46	95
121-674	SS 316 (coated)	Black	7	610	46	190